



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



GDB3.15A 250V Fa Low-Break IEC Glass Fuse

Bussmann Fuses

Catalog Number	GDB3.15A
Manufacturer	Bussmann Fuses
Description	Eaton GDB Series Fast-Acting Fuse 3.15A, 250 Vac or Less, 32 VDC (Self Certified), GDB-3-15a
Weight per unit	0.0050 (lbs/each)
Product Category	Small Dimension Fuses

Features

amperage rating	3.15 A
connection	Ferrule End X Ferrule End
dimensions	X X 0.7874 IN
interrupt rating	35 AIC at 250 Vac
Material	Glass tube Nickel-plated brass end cap construction
Voltage Rating	250 Vac or less, 32 Vdc (self certified)

Dimensions and Weight

Size	5.20 mm Diameter X 20.00 mm Height
------	------------------------------------

Descriptions

Description	250V FA LOW-BREAK IEC GLASS FUSE
extra long description	BUSS GDB-3.15A BUSS SMALL DIMENSION
Features	Fast-acting, low breaking capacity 5 mm x 20 mm ferrule fuse designed to IEC 60127-2 for overcurrent protection of electronic circuits. Install into a Bussmann Series fuse holder, block, or fuse clip, or purchase with available axial leads for thru-hole installation Eaton's GDB fast-acting, low breaking capacity 5mm x 20mm ferrule fuses are designed to IEC 60127-2 for overcurrent protection of electronic circuits. Order in cartridge fuse format and install into a Bussmann Series fuse holder, block, or fuse
Long Description	Eaton GDB Series Fast-acting fuse 3.15A, 250 Vac or less, 32 Vdc (self certified), GDB-3-15A
Product Type	Buss Small Dimension Fuse
Special Features	Low Breaking Capacity, Interrupt Rating 35 Amp at 250 V, Material Glass Tube, Nickel Plated Brass Endcap

Manufacturer Information

Brand	Eaton Bussmann series
GTIN	00051712431811
Manufacturers Part Number	GDB-3.15A
UPC	051712431811



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Taxonomies, Classifications, and Categories

Category Description	GLASS FUSES (and ceramic)
Type	Fast-Acting Fuse

Packaging

Carton	5
Weight Per each	0.005

Uses, Certifications, and Standards

Application	Ind Facilities & Factories - Facility: Safety and Security Systems
Frequency Rating	50
standard	VDE,CE Marked,RoHS Compliant,CCC Marked