



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



GFEP250 Type BR 30 Ma GFI BRKR 50A/2 Pole 120/240V 10K *Eaton Corp*

Catalog Number	GFEP250
Manufacturer	Eaton Corp
Description	Eaton BR Gfci Circuit Breaker, Industrial Ground Fault Thermal-Magnetic Equipment Protector, 50 A, 10 Kaic, Two-Pole, 120/240 V, Gfep, Common, #14-4 Awg, Ground Fault Circuit Interrupter, GFI
Weight per unit	0.8000 (lbs/each)
Product Category	20190104134007

Features

dimensions	5.7500 IN X 3.0000 IN X 4.5000 IN
interrupt rating	10
Poles	2
Voltage Rating	120/240 V

Descriptions

Description	TYPE BR 30 MA GFI BRKR 50A/2 POLE 120/240V 10K
extra long description	ETN GFEP250 BR 30 mA GFI 50A/2 Pole
Features	Eaton's BR circuit breakers are used in indoor and outdoor BR loadcenters, spa panels, meter breakers and sub panels. They are designed for a wide range of applications such as high short-circuit interrupt, series rating combinations with upstream main breakers, thermal magnetic, AFCI, GFCI, equipment protection and dual function AF/GF.
Long Description	Eaton BR GFCI circuit breaker,Industrial ground fault thermal-magnetic equipment protector,50 A,10 kAIC,Two-pole,120/240 V,GFEP,Common,#14-4 AWG,Ground fault circuit interrupter,GFI
Product Type	BR 30 Ma GFI 50A/2 Pole 120/240V 10K

Manufacturer Information

Brand	Eaton
GTIN	00786676092074
Manufacturers Part Number	GFEP250
UPC	786676092074

Taxonomies, Classifications, and Categories

Category Description	Fault Sensing Breakers (AFCI/GFCI)
Type	GFCI circuit breakers

Packaging

Carton	1
Weight Per each	0.8



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Uses, Certifications, and Standards

Application

OtherGeneration - Conventional Energy - Conventional
EnergyDatacenters - IT Space: CI and Hyper ConvergedMarine
Vessels and Equipment - Marine Vessels and Equipment -
OtherGeneration - Renewable Energy - Alternative Energy

standard

UL 489