

# Specifications

## Eaton GFTCB115

Eaton BR GFCI circuit breaker, Ground fault personnel protection circuit breakers, 15 A, 10 kAIC, Single-pole, 120/240 V, GFTCB, Ground fault circuit interrupter, GFI, 5 mA



### General specifications

<b>PRODUCT NAME</b>	Eaton BR GFCI circuit breaker
<b>CATALOG NUMBER</b>	GFTCB115
<b>UPC</b>	786680129766
<b>PRODUCT LENGTH/DEPTH</b>	6 in
<b>PRODUCT HEIGHT</b>	1.25 in
<b>PRODUCT WIDTH</b>	3.5 in
<b>PRODUCT WEIGHT</b>	0.475 lb
<b>CERTIFICATIONS</b>	UL 943 UL 489

## Product specifications

<b>TYPE</b>	Ground fault personnel protection circuit breakers
<b>AMPERAGE RATING</b>	15 A
<b>VOLTAGE RATING</b>	120/240 V
<b>CIRCUIT PROTECTION</b>	Ground fault circuit interrupter
<b>INDICATORS</b>	GFI
<b>PROTECTION</b>	5 mA
<b>INTERRUPT RATING</b>	10 kAIC
<b>MAIN CIRCUIT BREAKER</b>	GFTCB
<b>NUMBER OF POLES</b>	Single-pole

## Resources

### SPECIFICATIONS AND DATASHEETS

[Eaton Specification Sheet - GFTCB115](#)

### WARRANTY GUIDES

[Eaton type BR circuit breaker limited warranty June 2024](#)

**PROJECT NAME:**

**PROJECT NUMBER:**

**PREPARED BY:**

**DATE:**



**Eaton Corporation plc**  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com

© 2025 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.

Follow us on social media to get the latest product and support information.



# Specifications

## Eaton GFTCB115

Eaton BR GFCI circuit breaker, Ground fault personnel protection circuit breakers, 15 A, 10 kAIC, Single-pole, 120/240 V, GFTCB, Ground fault circuit interrupter, GFI, 5 mA



### General specifications

<b>PRODUCT NAME</b>	Eaton BR GFCI circuit breaker
<b>CATALOG NUMBER</b>	GFTCB115
<b>UPC</b>	786680129766
<b>PRODUCT LENGTH/DEPTH</b>	6 in
<b>PRODUCT HEIGHT</b>	1.25 in
<b>PRODUCT WIDTH</b>	3.5 in
<b>PRODUCT WEIGHT</b>	0.475 lb
<b>CERTIFICATIONS</b>	UL 943 UL 489

## Product specifications

<b>TYPE</b>	Ground fault personnel protection circuit breakers
<b>AMPERAGE RATING</b>	15 A
<b>VOLTAGE RATING</b>	120/240 V
<b>CIRCUIT PROTECTION</b>	Ground fault circuit interrupter
<b>INDICATORS</b>	GFI
<b>PROTECTION</b>	5 mA
<b>INTERRUPT RATING</b>	10 kAIC
<b>MAIN CIRCUIT BREAKER</b>	GFTCB
<b>NUMBER OF POLES</b>	Single-pole

## Resources

### SPECIFICATIONS AND DATASHEETS

[Eaton Specification Sheet - GFTCB115](#)

### WARRANTY GUIDES

[Eaton type BR circuit breaker limited warranty June 2024](#)

**PROJECT NAME:**

**PROJECT NUMBER:**

**PREPARED BY:**

**DATE:**



**Eaton Corporation plc**  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com

© 2025 Eaton. All Rights Reserved.

Eaton is a registered trademark. Follow us on social media to get the latest product and support information.

All other trademarks are property of their respective owners.

