



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



GFTCB215 Type BR 5 Ma GFI BRKR 15A/2 Pole 120/240V 10K

Eaton Corp

Catalog Number	GFTCB215
Manufacturer	Eaton Corp
Description	Eaton BR Gfci Circuit Breaker, Ground Fault Personnel Protection Circuit Breakers, 15 A, 10 Kaic, Two-Pole, 120/240 V, GFTCB, Common, #14-4 Awg, Ground Fault Circuit Interrupter, GFI
Weight per unit	0.8000 (lbs/each)
Product Category	In Circuit Breakers

Features

dimensions	4.5000 IN X 2.7500 IN X 2.0000 IN
interrupt rating	10
Poles	2
Voltage Rating	120/240 V

Descriptions

Description	TYPE BR 5 MA GFI BRKR 15A/2 POLE 120/240V 10K
extra long description	ETN GFTCB215 BR 5 MA GFI 15A/2 POLE
Features	Eaton's BR circuit breakers are used in indoor and outdoor BR loadcenters, spa panels, meter breakers and sub panels. They are designed for a wide range of applications such as high short-circuit interrupt, series rating combinations with upstream main breakers, thermal magnetic, AFCI, GFCI, equipment protection and dual function AF/GF.
Long Description	Eaton BR GFCI circuit breaker, Ground fault personnel protection circuit breakers, 15 A, 10 kAIC, Two-pole, 120/240 V, GFTCB, Common, #14-4 AWG, Ground fault circuit interrupter, GFI
Product Type	BR 5 Ma GFI 15A/2 Pole 120/240V 10K

Manufacturer Information

Brand	Eaton
GTIN	00786676025607
Manufacturers Part Number	GFTCB215
UPC	786676025607

Taxonomies, Classifications, and Categories

Category Description	Fault Sensing Breakers (AFCI/GFCI)
Type	GFCI circuit breakers

Packaging

Carton	1
Weight Per each	0.8



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Uses, Certifications, and Standards

Application

Marine Vessels and Equipment - Marine Vessels and Equipment -
Other Generation - Renewable Energy - Alternative
Energy Generation - Conventional Energy - Conventional
Energy Datacenters - IT Space: CI and Hyper Converged Other

standard

UL 489, UL 943