



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



GFTCB260 BR 5 Ma GFI BRKR 60A/2P 120/240V 10K Self Test Eaton Corp

Catalog Number	GFTCB260
Manufacturer	Eaton Corp
Description	Eaton BR Gfci Circuit Breaker, Ground Fault Personnel Protection Circuit Breakers, 60 A, 10 Kaic, Two-Pole, 120/240 V, GFTCB, Common, Plug-On, #14-4 Awg, Ground Fault Self Test, GFI
Weight per unit	0.8000 (lbs/each)
Product Category	In Circuit Breakers

Features

connection	Plug-on
dimensions	4.5000 IN X 2.0000 IN X 3.0000 IN
interrupt rating	10
Poles	2
Voltage Rating	120/240 V

Descriptions

Description	BR 5 MA GFI BRKR 60A/2P 120/240V 10K SELF TEST
extra long description	ETN GFTCB260 BR 5 MA GFI BREAKER 60
Features	Eaton's BR circuit breakers are used in indoor and outdoor BR loadcenters, spa panels, meter breakers and sub panels. They are designed for a wide range of applications such as high short-circuit interrupt, series rating combinations with upstream main breakers, thermal magnetic, AFCI, GFCI, equipment protection and dual function AF/GF.
Long Description	Eaton BR GFCI circuit breaker, Ground fault personnel protection circuit breakers, 60 A, 10 kAIC, Two-pole, 120/240 V, GFTCB, Common, Plug-on, #14-4 AWG, Ground fault self test, GFI
Product Type	BR 5 Ma GFI Breaker 60A/2P 120/240V 10K
Special Features	Ground Fault Self Test

Manufacturer Information

Brand	Eaton
GTIN	00786676025577
Manufacturers Part Number	GFTCB260
UPC	786676025577

Taxonomies, Classifications, and Categories

Category Description	Fault Sensing Breakers (AFCI/GFCI)
Type	GFCI circuit breakers



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Packaging

Carton	1
Package	10
Weight Per each	0.8

Uses, Certifications, and Standards

Application	OtherGeneration - Conventional Energy - Conventional EnergyDatacenters - IT Space: CI and Hyper ConvergedMarine Vessels and Equipment - Marine Vessels and Equipment - OtherGeneration - Renewable Energy - Alternative Energy
standard	UL 489,UL 943,Not Applicable