



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



GK6426 4-2/0 Cop Ground Conn Burndy LLC

Catalog Number	GK6426
Manufacturer	Burndy LLC
Description	Mechanical Grounding Connector, 3 Cables to Rod or Pipe, 4 Awg (Sol.) - 2/0 Awg (STR.), 3/8" Pipe, 5/8" - 3/4" Rod, 3/8" Stud.
Weight per unit	1.1 (lbs/each)
Product Category	Large Terminals & Connectors

Features

Bolt Size	3/8 in
Material	Copper Alloy, Cast

Descriptions

Description	4-2/0 COP GROUND CONN
extra long description	BUR GK6426 4-2/0 (3) CU .8 GRD
Long Description	Mechanical Grounding Connector, 3 Cables to Rod or Pipe, 4 AWG (Sol.) - 2/0 AWG (Str.), 3/8" Pipe, 5/8" - 3/4" Rod, 3/8" Stud.
Product Type	Mechanical
Special Features	Features: High Copper Alloy Ground Connector For Joining Three Equal Cables To Rod Or Tube, Cable Grooves Take A Wide Range Of Cable, High Copper Alloy Cast Body And DURIMUM U-Bolts, Nuts, And Lockwashers Make The GK Suitable For Direct Burial In Soil Or Concrete, One-Wrench Installation, UL467 Listed, Acceptable For Direct Burial In Earth Or Concrete, Tube (ips) Size: 3/8 IN, Ground Rod Size: 5/8 - 3/4 IN, Width: 3 IN, Installation Torque: 240 IN-LB, Height: 2-7/8 IN

Manufacturer Information

Brand	BURNDY
GTIN	00781810233528
Manufacturers Part Number	GK6426
UPC	781810233528

Taxonomies, Classifications, and Categories

Category Description	SERVICE ENTRANCE FITTINGS: Weatherheads & Grounding Fittings & Ground Rods
Type	Three Cables to Rod or Tube

Packaging

Carton	1
Weight Per each	1.0599



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Uses, Certifications, and Standards

Application

For Joining Three Equal Copper Cables To Rod Or Tube, Direct
Burial In Earth Or Concrete

standard

UL467