



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



GL2038 2/0 1-Hole Compression Lug 3/8" Bolt

Nsi Industries

| | |
|------------------|--|
| Catalog Number | GL2038 |
| Manufacturer | Nsi Industries |
| Description | 1 Holeshort Barrel Copper Compression Lug W/ PEEPHOLE2/0 Awg-3/8" Bolt Short Barrel Copper Compression Lugs With Peepholeis A Type Of Copper Compression Connector That Is Produced From High Conductivity Copper Tubing. They Are Tin-Plated to Provide Corrosion Resistance and Are Marked With Die Index and Color Coded For Easy Reference. Listed For 35KV Maximum When Properly Installed. |
| Weight per unit | 0.0600 (lbs/each) |
| Product Category | Large Terminals & Connectors |

Features

| | |
|-----------------|---------------|
| Cable Size | 2/0 AWG (STR) |
| Material | Copper |
| Number of Holes | 1 |
| Stud Size | 3/8 |
| Voltage Rating | 600 V |
| Warranty | 1 YEAR |

Material, Color, and Finish

| | |
|--------|------------|
| Color | Black |
| Finish | Tin Plated |

Dimensions and Weight

| | |
|------|-------------------------------------|
| Size | L=2.24 - W=.810 - OD=.560 - ID=.440 |
|------|-------------------------------------|



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Descriptions

| | |
|------------------------|--|
| Description | 2/0 1-HOLE COMPRESSION LUG 3/8" BOLT |
| extra long description | NSI GL2038 CU CMP Lug Short 2/0 AWG |
| Features | 1 HoleShort Barrel Copper Compression Lug w/ PeepHole2/0 AWG-3/8" Bolt Short Barrel Copper Compression Lugs with PeepHoleis a type of copper compression connector that is produced from high conductivity copper tubing. They are tin-plated to provide corrosion resistance and are marked with die index and color coded for easy reference. Listed for 35KV maximum when properly installed. |
| Long Description | 1 HoleShort Barrel Copper Compression Lug w/ PeepHole2/0 AWG-3/8" Bolt Short Barrel Copper Compression Lugs with PeepHoleis a type of copper compression connector that is produced from high conductivity copper tubing. They are tin-plated to provide corrosion resistance and are marked with die index and color coded for easy reference. Listed for 35KV maximum when properly installed. |
| Product Type | Cu CMP Lug Short 2/0 Awg 3/8 Bolt Size |
| Special Features | 2/0 AWG (STR) - 3/8 Mounting Hole |

Manufacturer Information

| | |
|---------------------------|----------------|
| Brand | NSi |
| GTIN | 00662381036094 |
| Manufacturers Part Number | GL2038 |
| UPC | 662381036094 |

Taxonomies, Classifications, and Categories

| | |
|----------------------|-----------------------------------|
| Category Description | Comp & Mech Lugs and Butt Splices |
| Type | Short Barrel - One Hole |

Packaging

| | |
|-----------------|------|
| Carton | 1 |
| Package | 25 |
| Weight Per each | 0.06 |

Uses, Certifications, and Standards

| | |
|--------------------------|---|
| Application | Terminate, Splice, Tap Power Connectors |
| environmental conditions | 90 C |
| Mounting | 3/8 Mounting Hole |
| standard | UL486A/B, UL467 (8 AWG -3/0 AWG) |