



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

210 Veterans Avenue
75672-0000, TX Marshall
Phone: 903-935-9535
Fax: 903-935-3490



GL6N141 #6 2H Cu SHRT CMP Lug

Nsi Industries

Catalog Number	GL6N141
Manufacturer	Nsi Industries
Description	2HOLESHORT Barrel Copper Compression Lug W/ PEEPHOLE6AWG-1/4" Bolt Short Barrel Copper Compression Lugs With Peepholeis A Type Of Copper Compression Connector That Is Produced From High Conductivity Copper Tubing. They Are Tin-Plated to Provide Corrosion Resistance and Are Marked With Die Index and Color Coded For Easy Reference. Listed For 35KV Maximum When Properly Installed.
Weight per unit	4.0 (lbs/each)
Product Category	Large Terminals & Connectors

Features

Cable Size	# 6 AWG (STR)
Material	Copper
Number of Holes	2
Stud Size	1/4
Voltage Rating	600 V
Warranty	1 YEAR

Material, Color, and Finish

Color	Blue
Finish	Tin Plated

Dimensions and Weight

Size	L=2.09 - W=.420 - OD=.300 - ID=.200
------	-------------------------------------



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

210 Veterans Avenue
75672-0000, TX Marshall
Phone: 903-935-9535
Fax: 903-935-3490

Descriptions

Description	#6 2H CU SHRT CMP LUG
extra long description	NSI GL6N-141 CMP Lug Cu Sht 6 AWG 1
Features	2HoleShort Barrel Copper Compression Lug w/ PeepHole6AWG-1/4" Bolt Short Barrel Copper Compression Lugs with PeepHoleis a type of copper compression connector that is produced from high conductivity copper tubing. They are tin-plated to provide corrosion resistance and are marked with die index and color coded for easy reference. Listed for 35KV maximum when properly installed.
Long Description	2HoleShort Barrel Copper Compression Lug w/ PeepHole6AWG-1/4" Bolt Short Barrel Copper Compression Lugs with PeepHoleis a type of copper compression connector that is produced from high conductivity copper tubing. They are tin-plated to provide corrosion resistance and are marked with die index and color coded for easy reference. Listed for 35KV maximum when properly installed.
Product Type	CMP Lug Cu SHT 6 Awg 1/4 BLT 5/8 SPC
Special Features	# 6 AWG (STR) - 1/4 Mounting Holes - 5/8 Hole Spacing

Manufacturer Information

Brand	Polaris
GTIN	00662381338006
Manufacturers Part Number	GL6N-141
UPC	662381338006

Taxonomies, Classifications, and Categories

Category Description	Comp & Mech Lugs and Butt Splices
Type	Short Barrel - Two Hole

Packaging

Carton	1
Package	100
Weight Per each	4

Uses, Certifications, and Standards

Application	Terminate, Splice, Tap Power Connectors
environmental conditions	90 C
Mounting	1/4 Mounting Holes
standard	UL486A/B, UL467 (8 AWG -3/0 AWG)