



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

5510 West 65th Street  
72209-0000, AR Little Rock  
Phone: 501-565-1785  
Fax: 501-565-0827



## GLC440DB BRZ GND Clamp

*Nsi Industries*

Catalog Number

GLC440DB

Manufacturer

Nsi Industries

Description

Nsi GLC-440DB Heavy Duty Direct Burial Ground Clamps Grip On Pipes Between 1-2-1/2" to 4" In Diameter and Are The Ultimate Ground Clamps For Securing Just About Any Size Ground Wire In Just About Any Application. The Bronze Body and Pre-Assembled 304 Stainless Steel Screws Are Made Of Economical, High-Quality Metals That Provide Durable Performance In A Range Of Applications. The Lay-In Lug Design Of These Clamps Provides Ultimate Flexibility When Securing Large Conductors and Can Accommodate Wires In The

Weight per unit

1.1 (lbs/each)

Product Category

Grounding & Bonding Equipment

### Features

Warranty

1 YEAR

### Material, Color, and Finish

Clamp Material

8 -4/0 STR

Insulation Material

Silicon Bronze



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

5510 West 65th Street  
72209-0000, AR Little Rock  
Phone: 501-565-1785  
Fax: 501-565-0827

## Descriptions

Description	BRZ GND CLAMP
extra long description	NSI GLC-440DB Ground Clamp Lay-In 2
Features	NSI grounding and bonding products rise to the occasion in a wide variety of indoor and outdoor environments with excellent material quality and flexible designs. These heavy-duty bronze ground clamps with lay-in lugs offer the ultimate solution for grounding large wires in just about any application. Grips onto copper water pipes, tubing, rebar and ground rods using 304 stainless steel screws to tighten the clamp, then grounding conductor is secured in place using a lay-in lug design for ultimate flexibility.
Long Description	NSI GLC-440DB Heavy Duty Direct Burial Ground Clamps grip on pipes between 1-2-1/2" to 4" in diameter and are the ultimate ground clamps for securing just about any size ground wire in just about any application. The bronze body and pre-assembled 304 stainless steel screws are made of economical, high-quality metals that provide durable performance in a range of applications. The lay-in lug design of these clamps provides ultimate flexibility when securing large conductors and can accommodate wires in the ground.
Product Type	Ground Clamp Lay-In 2 1/2-4" DB Rated
Special Features	2 1/2-4 Pipe Size

## Manufacturer Information

Brand	NSI
GTIN	00662381007193
Manufacturers Part Number	GLC-440DB
UPC	662381007193

## Taxonomies, Classifications, and Categories

Category Description	SERVICE ENTRANCE FITTINGS: Weatherheads & Grounding Fittings & Ground Rods
Type	Heavy Duty Direct Burial Lay-In Lug

## Packaging

Carton	1
Package	3
Weight Per each	1.1

## Uses, Certifications, and Standards

Application	Grounding Wire
standard	cULus