



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



GRP750 7.5" 50LB Natural CBL Tie *Nsi Industries*

Catalog Number	GRP750
Manufacturer	Nsi Industries
Description	The Powergrp GRP-750 100-Count Resealable Pack Of Type 21S Ah-2 Natural-Colored General-Purpose Cable Ties Are 7" Long, With 50LB Of Tensile Strength For Professional Applications. They're Made From Polyamide 6, 6 Nylon, Resulting In A High Mechanical Strength and A Wide Temperature Range (-40 F to 185 F). Fasten These 7" Cables Ties Around A Wide Range Of Equipment With A Bundle Diameter Between .12" (3MM) and 1.81" (46MM), Using The Bent Tips and Serrated Locking Mechanism to Form An Effortless and
Weight per unit	0.7900 (lbs/each)
Product Category	Tools & Testers

Features

Warranty	1 YEAR
----------	--------

Material, Color, and Finish

Finish	Natural
--------	---------

Descriptions

Description	7.5" 50LB NATURAL CBL TIE
extra long description	NSI GRP-750 PowerGRP Cbl Tie Natura
Features	PowerGRP cable ties are a comprehensive product line of specialty ties, strong enough to handle industrial environments and ideally suited for demanding applications. The GRP-750 ties combine a self-locking design with a general purpose 50lb tensile strength rating, guaranteeing that these ties won't break easily. The GRP in our name stands for Guaranteed Rugged and Powerful, just one way we show that we're fully committed to building strong ties for professional users. GRP-750 ties are waterproof and
Long Description	The PowerGRP GRP-750 100-Count Resealable Pack of Type 21S AH-2 Natural-Colored General-Purpose Cable Ties are 7" long, with 50lb of tensile strength for professional applications. They're made from polyamide 6,6 nylon, resulting in a high mechanical strength and a wide temperature range (-40 F to 185 F). Fasten these 7" cables ties around a wide range of equipment with a bundle diameter between .12" (3mm) and 1.81" (46mm), using the bent tips and serrated locking mechanism to form an effortless and
Product Type	Powergrp CBL Tie Natural 7.5" 50LB (100PK)



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Manufacturer Information

Brand	NSi
GTIN	00662381009104
Manufacturers Part Number	GRP-750
UPC	662381009104

Taxonomies, Classifications, and Categories

Category Description	Screws, Bolts, Staples, Jack Chains, Washers & TY-Raps
----------------------	--

Availability

minimum qty	100
-------------	-----

Packaging

Carton	1
Package	100
Weight Per each	0.79

Uses, Certifications, and Standards

Temperature Rating	-40F to 185F
--------------------	--------------