




# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## H100X034H1T 3/16 HTSHK LBL Panduit Corporation

Catalog Number	H100X034H1T
Manufacturer	Panduit Corporation
Description	The H100X034H1T Military-Grade Polyolefin Heat-Shrink Label Is Single-Sided Printable. It Offers Crisp, Clear Legends With Superior Readability For Quick and Easy Label Production. The Heat-Shrink Sleeve Is Designed to Provide A Clear, Reliable, and Durable Way to Identify Wires and Cables. Shrink Ratio 3:1. 0.34" X 1" (8.6 MM X 25.4 MM). Color White. 1000 Labels Per Roll.
Weight per unit	2.3 (lbs/each)
Product Category	Markers & Marking Tapes

### Features

labels per package	1000
Material	Polyolefin
Printer Type	THERMAL TRANSFER
Temperature Range	275

### Material, Color, and Finish

Color	White
-------	-------

### Dimensions and Weight

Length	NA
Size	1.00 x 0.34
Width	1

### Descriptions

Description	3/16 HTSHK LBL
extra long description	PAN H100X034H1T H100X034H1T Heatshr
Long Description	The H100X034H1T Military-Grade Polyolefin Heat-Shrink Label is single-sided printable. It offers crisp, clear legends with superior readability for quick and easy label production. The heat-shrink sleeve is designed to provide a clear, reliable, and durable way to identify wires and cables. Shrink ratio 3:1. 0.34" x 1" (8.6 mm x 25.4 mm). Color White. 1000 labels per roll.
Product Type	H100X034H1T Heatshrink, Po, White, Mil Grade, 1000 LBLs, TT,

### Manufacturer Information

Brand	PANDUIT
GTIN	00074983522156
Manufacturers Part Number	H100X034H1T-2-B
UPC	074983522156



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Taxonomies, Classifications, and Categories

Category Description	HEAT/COLD SHRINK
Type	Heat Shrink Label

## Packaging

Carton	5
Package	1
Weight Per each	2.3499

## Uses, Certifications, and Standards

standard	Meets UL Standard 224 for flammability and AMS-DTL-23053/5C (Class 1 and Class 3). Meets SAE-AS81531, MIL-STD-883F Method 2015.13, Solutions A, B, and D, and D202F, and MIL-STD-202G Method 215K, Solutions A, C, and D when printed with resin or hybrid therm
----------	--