



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## **HBL1556I Mom Tog, 15A, 120/277V, SPDT, Iv** *Hubbell Wiring Devices*

Catalog Number	HBL1556I
Manufacturer	Hubbell Wiring Devices
Description	Switches and Lighting Controls, Industrial Grade, Toggle Switches, General Purpose Ac, Momentary Single Pole Double Throw Center Off, 15A 120/277V Ac, Terminal Screws, Ivory Toggle
Weight per unit	0.0720 (lbs/each)
Product Category	Gen Purpose Switches

### **Features**

action	SPDT
amperage rating	15
connection	Back and Side Wired
Contact Configuration	Momentary
Contact Rating	Per UL 20
Current Rating	15
insulation	False
operating cycles	50,000
pallet quantity	4500
Poles	Single Pole
Switch Type	Toggle
Voltage Rating	120-277
Wattage	4155

### **Dimensions and Weight**

Size	4.06 in x 1.31 in x 1.89 in
------	-----------------------------

### **Descriptions**

Description	MOM TOG, 15A, 120/277V, SPDT, IV
extra long description	HWDK HBL1556I MOM TOG, 15A, 120/277
Long Description	Switches and Lighting Controls, Industrial Grade, Toggle Switches, General Purpose AC, Momentary Single Pole Double Throw Center Off, 15A 120/277V AC, Terminal Screws, Ivory Toggle
Product Type	Mom Tog, 15A, 120/277V, SPDT, Iv
Special Features	Momentary Contact



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Manufacturer Information

Brand	WIRING DEVICE-KELLEMS
GTIN	00783585432786
Manufacturers Part Number	HBL1556I
series	Extra Heavy Duty
UPC	783585432786

## Taxonomies, Classifications, and Categories

Category Description	Industrial switches
Type	TOGGLE

## Packaging

Carton	1
Package	10
Weight Per each	0.072

## Uses, Certifications, and Standards

Application	Back and Side Wired
Enclosure	None
environmental conditions	Indoor Dry unless protected by additional means
Mounting	Screw Mount
standard	UL Listed