



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



HBL2740 LKG RCPT, 30A 3P 600V, L17-30R, BK *Hubbell Wiring Devices*

| | |
|------------------|--|
| Catalog Number | HBL2740 |
| Manufacturer | Hubbell Wiring Devices |
| Description | Locking Devices, Twist-Lock®, Industrial, Flush Receptacle, 30A 3-Phase Delta 600V Ac, 3-Pole 4-Wire Grounding, L17-30R, Screw Terminal, Black |
| Weight per unit | 0.0810 (lbs/each) |
| Product Category | Gen Purpose Recept & Surge Pro |

Features

| | |
|---------------------|---------------------------|
| amperage rating | 30 |
| connection | Screw Terminal |
| Current Rating | 30 |
| Dielectric Strength | Withstands 2,000V minimum |
| Material | Nylon |
| Number of Wires | 4-Wire |
| pallet quantity | 2730 |
| Phase | 3 |
| Poles | 3-Pole |
| Voltage Rating | 3 Phase 600 VAC |
| Wattage | 18,000 |
| Wire Size | #16 to #8 |

Dimensions and Weight

| | |
|------|----------------------------|
| Size | 3.28 in x 1.7 in x 1.31 in |
|------|----------------------------|

Descriptions

| | |
|------------------------|--|
| Description | LKG RCPT, 30A 3P 600V, L17-30R, BK |
| extra long description | HWDK HBL2740 LKG RCPT, 30A 3P 600V, |
| Long Description | Locking Devices, Twist-Lock®, Industrial, Flush Receptacle, 30A 3-Phase Delta 600V AC, 3-Pole 4-Wire Grounding, L17-30R, Screw Terminal, Black |
| Product Type | LKG RCPT, 30A 3P 600V, L17-30R, BK |
| Special Features | Standard |

Manufacturer Information

| | |
|---------------------------|-----------------------|
| Brand | WIRING DEVICE-KELLEMS |
| GTIN | 00783585236179 |
| Manufacturers Part Number | HBL2740 |
| UPC | 783585236179 |



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Taxonomies, Classifications, and Categories

| | |
|----------------------|-------------------------|
| Category Description | Residential Switches |
| Type | Single Flush Receptacle |

Packaging

| | |
|-----------------|-------|
| Carton | 1 |
| Package | 10 |
| Weight Per each | 0.081 |

Uses, Certifications, and Standards

| | |
|--------------------------|---|
| Application | Heavy Duty Industrial |
| environmental conditions | Indoor Dry unless protected by additional means |
| Mounting | Screw Mount |
| nema rating | L17-30R |
| standard | Certified to CSA C22.2 No.42;Fed.Spec. W-C-596;Listed to UL 498 |