



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



HBL8300HI Dup RCPT, Com/HG, 20A 125V, 5-20R, Iv *Hubbell Wiring Devices*

Catalog Number	HBL8300HI
Manufacturer	Hubbell Wiring Devices
Description	Straight Blade Devices, Receptacles, Duplex, Compact Hospital Grade, 2-Pole 3-Wire Grounding, 20A 125V, 5- 20R, Ivory, Single Pack.
Weight per unit	0.2000 (lbs/each)
Product Category	Gen Purpose Recept & Surge Pro

Features

amperage rating	20
connection	Back and Side Wired Screw Terminals
Current Rating	20
Dielectric Strength	Withstands 2,000V minimum
Number of Wires	3-Wire
pallet quantity	3600
Phase	1
Poles	2-Pole
Voltage Rating	125 V
Wattage	2500
Wire Size	#12 to #10

Dimensions and Weight

Size	3.28 in x 1.33 in x 1.05 in
------	-----------------------------

Descriptions

Description	DUP RCPT, COM/HG, 20A 125V, 5-20R, IV
extra long description	HWDK HBL8300HI DUP RCPT, COM/HG, 20
Features	HBL® Extra Heavy Duty Max Hospital Grade Devices - UL requirements for Hospital Grade devices is more stringent than those for standard devices. Hubbell receptacles are designed to meet and exceed the standards with Exclusive nickel-plated bypass contact design increases contact pressure, lowering the operating temperature; Four point grounding system provides redundant grounding for low resistance ground continuity in high abuse areas; Impact resistant deep face design prevents breakage. Because of these
Long Description	Straight Blade Devices, Receptacles, Duplex, Compact Hospital Grade, 2-Pole 3-Wire Grounding, 20A 125V, 5- 20R, Ivory, Single Pack.
Product Type	Dup RCPT, Com/HG, 20A 125V, 5-20R, Iv
Special Features	Self Grounding



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Manufacturer Information

Brand	WIRING DEVICE-KELLEMS
GTIN	00783585015675
Manufacturers Part Number	HBL8300HI
series	Hospital Grade
UPC	783585015675

Taxonomies, Classifications, and Categories

Category Description	Industrial receptacles
Type	RECEPTACLE

Packaging

Carton	1
Package	10
Weight Per each	0.2

Uses, Certifications, and Standards

Application	Slender/Compact Hospital Grade
environmental conditions	Indoor Dry unless protected by additional means
Mounting	Screw Mount
nema rating	5-20R
standard	CSA Certified, C22.2, No. 42 File 285;Fed. Spec. W-C-596;NEMA® WD-6 Compliant;UL Listed to UL498 File No. E2186