



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## HCTR4 4A 600V Class CC Time Delay Small Control Fuse

*Edison Fuses*

Catalog Number	HCTR4
Manufacturer	Edison Fuses
Description	Eaton Edison HCTR Fuse, Non-Indicating, 4 A, Class CC, 200 Kaic, Standard, 10, 600 V
Weight per unit	0.0300 (lbs/each)
Product Category	Dual Element

### Features

amperage rating	4
dimensions	1.0000 IN X 0.4060 IN X 0.4060 IN
Fuse Class	Class CC
interrupt rating	200 kAIC
media	Yes
Voltage Rating	600 V

### Dimensions and Weight

Height	0.406
Length	1
Width	0.406

### Descriptions

Description	4A 600V CLASS CC TIME DELAY SMALL CONTROL FUSE
extra long description	BUSS HCTR4 UL CLASS CC TIME DELAY
Features	Edison offers a complete line of Class CC fuses to meet your circuit and equipment protection needs. These branch circuit rated compact fuses rated 600v, and delivering 200,000a IR Vac Sym provide excellent protection in the smallest package of any UL class of fuses. Choose from our EDCC time-delay fuses for your small horsepower motor circuits, our HCLR fast-acting for your non-inductive lighting and resistance heating loads or our HCTR time-delay fuses for your small control transformer protection.
Long Description	Eaton Edison HCTR fuse, Non-indicating, 4 A, Class CC, 200 kAIC, Standard, 10, 600 V
Product Type	UI Class CC Time Delay
Special Features	Non-Indicating

### Manufacturer Information

Brand	Eaton
GTIN	00782634802228
Manufacturers Part Number	HCTR4
UPC	782634802228



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Taxonomies, Classifications, and Categories

Category Description	MIDGET FUSES
Type	FUSE

## Packaging

Carton	1
Package	10
Weight Per each	0.03

## Uses, Certifications, and Standards

Application	Datacenters - Facilities: Critical Power
standard	UL Listed ,CSA Certified,CE Marked,RoHS Compliant