



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## HEBAWRLCB 30A In-Line Buss Fuseholder

*Bussmann Fuses*

Catalog Number	HEBAWRLCB
Manufacturer	Bussmann Fuses
Description	Fuse Holder, In-Line, Breakaway Type; UI, Ce Approval; 600 Volt Voltage Rating; 1 Pole(S); Crimp (Line/Load) Terminal Type; 13/32 Inch X 1-1/2 Inch Fuse Type; 30 Amp Fuse Current Rating; (2) 16 to 12 Awg, 16 to 8 Awg (Copper) Load Wire Size
Weight per unit	2.5 (lbs/each)
Product Category	Fuseholders & Fuseblks

### Features

Fuse Current Rating	30 Amp
Fuse Type	13/32 INCH X 1-1/2 INCH
Line Wire Size	(2) 10 AWG, 6 AWG (Copper)
Load Wire Size	(2) 16 to 12 AWG, 16 to 8 AWG (Copper)
Poles	1
Terminal Type	Crimp (Line/Load)
Voltage Rating	600 Volt

### Descriptions

Additional Information	RoHS Compliant; Temperature Rating -40 to 221 Deg F
Commodity Description	FUSEHOLDERS & FUSEBLOCKS
Description	30A IN-LINE BUSS FUSEHOLDER
extra long description	IN-LINE, BREAKAWAY TYPE; UL, CE APPROVAL; 600 VOLT VOLTAGE RATING; 1 POLE(S); CRIMP (LINE/LOAD) TERMINAL TYPE; 13/32 INCH X 1-1/2 INCH FUSE TYPE; 30 AMP FUSE CURRENT RATING; (2) 16 TO 12 AWG, 16 TO 8 AWG (COPPER) LOAD WIRE SIZE; (2) 10 AWG, 6 AWG (COPPER) LINE WIRE SIZE; ROHS COMPLIANT; TEMPERATURE RATING -40 TO 221 DEG F; HEB MODEL
Long Description	FUSE HOLDER, IN-LINE, BREAKAWAY TYPE; UL, CE APPROVAL; 600 VOLT VOLTAGE RATING; 1 POLE(S); CRIMP (LINE/LOAD) TERMINAL TYPE; 13/32 INCH X 1-1/2 INCH FUSE TYPE; 30 AMP FUSE CURRENT RATING; (2) 16 TO 12 AWG, 16 TO 8 AWG (COPPER) LOAD WIRE SIZE
Product Type	Fuse Holder



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Manufacturer Information

Brand	Bussmann Fuses
GTIN	00051712718523
Manufacturers Part Number	HEB-AW-RLC-B
Model	HEB
UPC	051712718523

## Taxonomies, Classifications, and Categories

Type	In-Line, Breakaway
------	--------------------

## Availability

Manufacturer Status	Non-Stock
---------------------	-----------

## Packaging

Carton	1
Weight Per each	2.5

## Uses, Certifications, and Standards

Approval	UL, CE
----------	--------