


RESIDENTIAL DIMMERS & FAN SPEED CONTROLS



Harmony® Incandescent and Low Voltage Dimmers



H703PW

H1103PLA

HLV703PW

HLV1103PLA

Features

- Convenient operation – combines ON/OFF Decorator switch with separate slider for dimming control.
- Green LED glows when OFF to make dimmer easy to find in the dark.
- Constant memory returns lights to previous level after a power failure.
- Sleek, ergonomic P&S Decorator style matches other Decorator devices.
- Higher ratings.
- Single pole and 3-way operation.
- Works with standard 3-way switches and wiring.
- Screw-pressure-plate back wire terminals save time, space and money.
- No de-rating.
- No fins to break.

H703P, HLV703P

Interchangeable Face Versions

- Package comes with three face colors – Ivory, White, Light Almond (TC).
- White only option also available.
- Interchangeable faces available in ten colors (sold separately, see below).

CATALOG NUMBER	DESCRIPTION	RATINGS	COLOR
INCANDESCENT SINGLE POLE/3-WAY DIMMERS*			
H703PW H703PABCCV4 H703PDBCCV4 H703PNICCV4	Incandescent Preset, Single Pole and 3-Way	120V, 700W	White Antique Brass Dark Bronze Nickel
H1103PW	Incandescent Preset, Single Pole and 3-Way	120V, 1100W	White
INTERCHANGEABLE FACE INCANDESCENT SINGLE POLE/3-WAY DIMMERS			
H703PTC	Incandescent Preset, Single Pole and 3-Way Three Interchangeable Face Colors	120V, 700W	Ivory/White/Light Almond
H1103PTC	Incandescent Preset, Single Pole and 3-Way Three Interchangeable Face Colors	120V, 1100W	Ivory/White/Light Almond
MAGNETIC LOW VOLTAGE PRESET, SINGLE POLE/3-WAY			
HLV703PTC	Preset, Single Pole/3-Way Three Interchangeable Face Colors	120V, 700VA	Ivory/White/Light Almond
HLV703PW	Preset, Single Pole/3-Way		White
HLV1103PTC	Preset, Single Pole/3-Way Three Interchangeable Face Colors	120V, 1100VA	Ivory/White/Light Almond
HLV1103PW	Preset, Single Pole/3-Way		White
INTERCHANGEABLE FACE COVERS†			
HKITI HKITW HKIT HKITGRY HKITBK HKITLA HKITTI HKITAB HKITDB HKITNI	Harmony® Interchangeable Face		Ivory White Brown Gray Black Light Almond Titanium Antique Brass Dark Bronze Nickel


*Available in VisionPak™ packaging, add "CCV6" to Catalog Number. Example: H1103PWCCV6.

†Available in VisionPak™ packaging, add "BPCCV6" to Catalog Number. Example: HKITBPCCV6.


DEVICES & WALL PLATES

Color Selection Chart

Devices & Plastic Wall Plate Colors



Ivory Light Almond White Green Antique Brass Dark Bronze Nickel




Black Blue Brown Gray Orange Red

See specific device and wall plate catalog charts for particular color availabilities.

Metal Wall Plates


Metal Finish




Aluminum Brass (Brushed) Polished Brass Stainless Steel Brushed Bronze Chrome

Custom Metal Wall Plates Paint Finish Colors

Paint Color



Orange Green Gray Yellow Glossy Black Brown White



Primer Red Pink Flat Black Ivory Light Almond Blue

To order custom metal wall plates, see Pages P-40 – P-42.

For additional colors consult factory.