



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## HLBSL4069FS351EM \*Discontinued\* 4" Led Trim 3K/4K/5K Ultra Thin *Cooper Lighting Solutions*

Catalog Number	HLBSL4069FS351EM
Manufacturer	Cooper Lighting Solutions
Description	4-Inch Led Smooth Lens Downlight With Plastic Housing and Remote Driver / Junction Box With Selectable CCT (3000K-5000K)
Weight per unit	0.5100 (lbs/each)
Product Category	Lighting

### Features

amperage rating	0.085 A at 120 V
Lamp Type	LED
Socket Type	N/A
Voltage Rating	120V
Wattage	10.1 W

### Material, Color, and Finish

Finish	white
Style	(blank)

### Descriptions

Description	*DISCONTINUED* 4" LED TRIM 3K/4K/5K ULTRA THIN
extra long description	CLS HLBSL4069FS351EMWR 4" RD SFT LE
Long Description	4-Inch LED smooth lens downlight with plastic housing and remote driver / junction box with Selectable CCT (3000K-5000K)
Product Type	4" RD SFT Lens, 600LM, 30-50K, 120V, MW
Special Features	Features a round polymer trim and smooth lens

### Manufacturer Information

Brand	HALO
GTIN	00080083916368
Manufacturers Part Number	HLBSL4069FS351EMWR
UPC	080083916368

### Taxonomies, Classifications, and Categories

Category Description	LED ARCHITECTURAL & SPECIFICATION LIGHTING
Type	HLBSL Smooth Lens Downlight

### Packaging

Carton	1
Package	4
Weight Per each	0.51



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Uses, Certifications, and Standards

Application	lighting
Mounting standard	Direct Mount Energy Star Certified;IECC Compliant;Title 24 Compliant;UL Certified - Damp Location;RoHS Compliant;Showerlight;AIR-TITE (TM) Certified ASTM E283;Wet Locations Listed;LM79/LM80 Compliant;EMI/RFI per FCC 47CFR Part 15 B;California Title 24;IP44 Rated