



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

1336 Swisco Road
70665-0000, LA Sulphur
Phone: 337-533-8019
Fax: 337-533-8055



HP402442 400A PNL 400A MCB W/24/42 Dist & No Prov For Sec M *Eaton Corp*

Catalog Number	HP402442
Manufacturer	Eaton Corp
Description	Eaton House Panel, 400A, Aluminum, No Bypass, Nema 3R, Underground, 22 Kaic, Lug Landings For Compression, Lugs Not Included, DK2400, Surface Mounting, C:42, S:1, SP:24, None, Ring, Type BR Breakers, 120/240V, 4306, Single-Phase
Weight per unit	120.0 (lbs/each)
Product Category	Residential Meter Socket Circu

Features

amperage rating	400
interrupt rating	10
number of spaces	24
Voltage Rating	120/240 V

Dimensions and Weight

Depth	6
Height	44
Width	29.75

Descriptions

Description	400A PNL 400A MCB W/24/42 DIST & NO PROV FOR SEC M
extra long description	ETN HP402442 400A PNL,400A MCB W/24
Features	Eaton's House Panel service entrance devices consist of a meter socket and a distribution section. They offer fast, easy and safe installation. Available in CH and BR styles. In addition to residential installations, a house panel can also be used for an apartment, condominium, clubhouse or common area.
Long Description	Eaton house panel, 400A, Aluminum, No bypass, NEMA 3R, Underground, 22 kAIC, Lug landings for compression, lugs not included, DK2400, Surface mounting, C:42, S:1, SP:24, None, Ring, Type BR breakers, 120/240V, 4306, Single-phase
Product Type	400A PNL, 400A MCB W/24/42 Dist, 22K

Manufacturer Information

Brand	Eaton
GTIN	00786676000567
Manufacturers Part Number	HP402442
UPC	786676000567

Taxonomies, Classifications, and Categories

Category Description	PANELBOARD BOXES & INTERIORS
Type	House panel



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

1336 Swisco Road
70665-0000, LA Sulphur
Phone: 337-533-8019
Fax: 337-533-8055

Packaging

Carton	1
Weight Per each	120

Uses, Certifications, and Standards

Application	Residential Bldgs & Facilities - Residential Bldgs & Facilities - Other
Mounting	Surface Mount
standard	UL Listed,EUSERC Approved