



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## HUB150DN 1-1/2" Rigid Watertite D/C Hub

*Appleton/Oz Gedney*

Catalog Number	HUB150DN
Manufacturer	Appleton/Oz Gedney
Description	Watertight Hubs, Zinc Diecast Hubs - Insulated, Class I, Div 2, Trade Size: 1-1/2", Body Length: 1.12", Thread Length: 0.78", Outside Diameter: 2.75"
Weight per unit	0.7000 (lbs/each)
Product Category	Rigid Conduit Fittings - Steel

### Features

Material	Zinc Die Cast
----------	---------------

### Dimensions and Weight

Size	1-1/2
------	-------

### Descriptions

Description	1-1/2" RIGID WATERTITE D/C HUB
extra long description	EGS HUB150DN 1-1/2 ZDC WATER TIGHT
Long Description	Watertight Hubs, Zinc Diecast Hubs - Insulated, Class I, Div 2, Trade Size: 1-1/2", Body Length: 1.12", Thread Length: 0.78", Outside Diameter: 2.75"
Product Type	1-1/2 ZDC Water Tight Hubs
Special Features	1-1/2 IN Trade Size Hub, Hole Dia. Min 1.92 IN, Hole Dia. Max 2.02 IN, Panel Thickness Min. 0.06 IN, Panel Thickness Max. 0.25 IN, Insulated Throat

### Manufacturer Information

Brand	Appleton
GTIN	00687855002153
Manufacturers Part Number	HUB150DN
UPC	687855002153

### Taxonomies, Classifications, and Categories

Category Description	Watertight Hub, 3-PIECE COUPLINGS, THREADLESS COUPLINGS AND THREADLESS CONNECTOR
Type	Watertight Hubs

### Packaging

Carton	10
Package	50
Weight Per each	0.7



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Uses, Certifications, and Standards

Application

Used to Connect Rigid or IMC Conduit to a Threadless Opening in an Enclosure

standard

CSA Certified: 065178; CSA Standard: C22.2 No. 18.3; NEMA: FB-1; UL Listed: E14814; UL Standard: 514B