



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## IPL43 #4-#14 3 Pole Polaris Connector Block

*Nsi Industries*

Catalog Number	IPL43
Manufacturer	Nsi Industries
Description	Single Sided Entry Insulated Multi-Tap Connector, #14 Awg (Stranded) Conductor Size, #4 Awg (Stranded) Conductor Size, Insulated, Plastisol Insulation Material, Copper/Aluminum Conductor Material, Black Insulation Color, 3 Conductors, -45 °C Operating Temperature, +90 °C Operating Temperature, 1.55 In Overall Length, 600 V, 0.08 LB/Ea
Weight per unit	0.0800 (lbs/each)
Product Category	Large Terminals & Connectors

### Features

Material	Aluminum
Poles	1
Voltage Rating	600 V
Warranty	1 YEAR
Wire Size	4-14 AWG
Wire Type	Class B & C

### Material, Color, and Finish

Color	Black
Finish	Plastisol Insulated

### Dimensions and Weight

Size	L=1.550 - W=1.188 - H=1.375
------	-----------------------------

### Descriptions

Description	#4-#14 3 POLE POLARIS CONNECTOR BLOCK
extra long description	NSI IPL4-3 POLARIS Ins Multi-Tap 4
Features	The Polaris IPL4-3 3-Port Single-Side Connector provides the simplest solution for forming a secure connection between up to three conductors in applications including cable trays, panel boards, ducts, raceways or troughs. Sized for 4-14 AWG wires and rated for 600V, this pre-insulated connector comes pre-loaded with an oxide inhibitor and installs faster than traditional uninsulated connector options using just a hex key and torque wrench. The aluminum alloy body is wrapped in high-dielectric strength pla

### Manufacturer Information

GTIN	00662381910011
UPC	662381910011



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Taxonomies, Classifications, and Categories

Category Description ..... SPLIT BOLTS

Type ..... Single Sided Entry

## Packaging

Carton ..... 12

Weight Per each ..... 0.08

## Uses, Certifications, and Standards

Application ..... Wire Termination

environmental conditions ..... 90 C

standard ..... UL 486A/B

Temperature Rating ..... 90 C