



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## J2139NE 9" Journeyman Pliers Side Cutting

*Klein Tools*

Catalog Number	J2139NE
Manufacturer	Klein Tools
Description	Cutting Plier, Steel Blade Material, 25/32 In Blade Length, Hardened Tool Steel Handle Material, Dark Blue/Black (Handle), Journeyman (Handle), 9-1/2 In Overall Length, 1-19/32 In Jaw Length, 1-1/4 In Jaw Width, 1.1 LB
Weight per unit	1.1 (lbs/each)
Product Category	Pliers, Wrenches, Saw, Pouches

### Features

Handle Length	5.55" (14.1 cm)
jaw thickness	0.62" (1.6 cm)
knife length	0.781" (2 cm)
Material	Induction Hardened Steel
media	Yes
Overall Height	0.75" (1.9 cm)
Overall Width	2.29" (5.8 cm)
tether capable	No

### Material, Color, and Finish

Handle Color	DARK BLUE/BLACK
--------------	-----------------

### Descriptions

Also Known As...	Rabbit Ears Pliers Linesman's Pliers Diagonal cutters Loppers
Description	9" JOURNEYMAN PLIERS SIDE CUTTING
extra long description	KLEIN J213-9NE Journeyman™ Side Cut
Features	These Klein Tools 9-Inch Journeyman pliers are induction hardened and have a hot-riveted joint for smooth and powerful action without handle wobble. Their streamlined design is paired with their cross-hatched knurled jaws for confident gripping. And their unique tempered handle design, with dual material Journeyman handles provide a better grip and absorbs the snap when using their side-cutting capabilities.
similar brands	kleins

### Manufacturer Information

GTIN	00092644721014
UPC	092644721014



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Taxonomies, Classifications, and Categories

Category Description ..... HAND TOOLS

Type ..... Side Cutting Pliers

## Packaging

Carton ..... 1

Package ..... 6

Weight Per each ..... 1.13

## Uses, Certifications, and Standards

Application ..... General Purpose

standard ..... Y