



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## **KTALED40D2DWM85 40W Dusk to Dawn Led Barn Area Light 5K 120/277V** *Keystone Technologies*

Catalog Number	KTALED40D2DWM85
Manufacturer	Keystone Technologies
Description	40W Dusk to Dawn Led Area Light. 120-277V Input, 5000K, Includes Nema Type 3-Pin Twist Lock Photocell, Type V Optics, 0-10V Dimmable. Standard Gray Housing
Weight per unit	1.8 (lbs/each)
Product Category	Lighting

### **Features**

Ballast Type	N/A
beam angle	N/A
Circuit Type	N/A
Input Voltage	120-277V
ip rating	IP65
lumens	6150
Nominal Length	N/A
Nominal Size	Small Housing
Number of Lamps	N/A
Output Current	N/A
Output Voltage	N/A
Sensor Type	Photocell
Wattage	40
Wire Type	N/A

### **Material, Color, and Finish**

Base Type	N/A
color rendering index (cri)	>80 Deg
color temperature	5000
housing color	Gray

### **Descriptions**

Construction	N/A
Description	40W DUSK TO DAWN LED BARN AREA LIGHT 5K 120/277V
extra long description	Key KT-ALED40-D2D-WM-850-VDIM Power
Long Description	40W Dusk to Dawn LED Area Light. 120-277V Input, 5000K, Includes NEMA Type 3-pin Twist Lock Photocell, Type V Optics, 0-10V Dimmable. Standard Gray Housing
Product Type	Power Selectable Stocking Special, 9250/6850/5200 Lumens CO



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Manufacturer Information

Brand	Keystone
GTIN	00843654131610
Manufacturers Part Number	KT-ALED40-D2D-WM-850-VDIM
UPC	843654131610

## Taxonomies, Classifications, and Categories

Category Description	LED CANOPY, PARKING, POLE MOUNTED & ROADWAY LIGHTING
----------------------	--

## Packaging

Carton	1
Package	2
Weight Per each	1.8

## Uses, Certifications, and Standards

Energy Star	N
-------------	---