



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

8420 Tejas Loop
78045-0000, TX Laredo
Phone: 956-462-0607
Fax: 956-284-6601



L12T836GC850DX2 12W Led T8 36" 50K Line DBL/SNGL Ended *Keystone Technologies*

| | |
|------------------|---|
| Catalog Number | L12T836GC850DX2 |
| Manufacturer | Keystone Technologies |
| Description | 12W Led T8 Tube, Shatter-Proof Coated Glass, 120-277V Input, 3, 5000K, Direct Drive, Single or Double Ended |
| Weight per unit | 0.5600 (lbs/each) |
| Product Category | Shape & Circular Lamps |

Features

| | |
|-----------------|----------|
| Ballast Type | N/A |
| beam angle | 240 |
| Circuit Type | N/A |
| Input Voltage | 120-277V |
| ip rating | N/A |
| lumens | 1500 |
| Nominal Length | 36 in |
| Nominal Size | N/A |
| Number of Lamps | N/A |
| Output Current | N/A |
| Output Voltage | N/A |
| Sensor Type | N/A |
| Warranty | 5 |
| Wattage | 12 |
| Wire Type | N/A |

Material, Color, and Finish

| | |
|-----------------------------|---------|
| Base Type | G13 |
| color rendering index (cri) | >80 Deg |
| color temperature | 5000 |
| housing color | N/A |

Descriptions

| | |
|------------------------|---|
| Description | 12W LED T8 36" 50K LINE DBL/SNGL ENDED |
| extra long description | Key KT-LED12T8-36GC-850-DX2-CP 12W |
| Long Description | 12W LED T8 TUBE, SHATTER-PROOF COATED GLASS, 120-277V INPUT, 3, 5000K, DIRECT DRIVE, SINGLE OR DOUBLE ENDED |
| Product Type | 12W Led T8 Tube, Shatter-Proof Coated Glass, 120-277V Input, |



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

8420 Tejas Loop
78045-0000, TX Laredo
Phone: 956-462-0607
Fax: 956-284-6601

Manufacturer Information

| | |
|---------------------------|-----------------------------|
| Brand | Keystone |
| GTIN | 00890949019238 |
| Manufacturers Part Number | KT-LED12T8-36GC-850-DX2 /G2 |
| UPC | 890949019238 |

Taxonomies, Classifications, and Categories

| | |
|----------------------|--|
| Category Description | LED LINEAR STRAIGHT(Fluor replacement), U-SHAPE & CIRCULAR LAMPS |
|----------------------|--|

Packaging

| | |
|-----------------|------|
| Carton | 25 |
| Weight Per each | 0.56 |

Uses, Certifications, and Standards

| | |
|-------------|---|
| Energy Star | Y |
|-------------|---|