



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



L18.5T848GC850DX 18.5W Led T8 48" 50K Line DBL/SNGL Ended GC 2600LM *Keystone Technologies*

| | |
|------------------|---|
| Catalog Number | L18.5T848GC850DX |
| Manufacturer | Keystone Technologies |
| Description | 18.5W Led T8 Tube, Glass Construction, 4FT, 5000K, 120-277V Input, 25 PCS Carton, Direct Drive Single or Double Ended. Gen.2 |
| Weight per unit | 0.6600 (lbs/each) |
| Product Category | 20200107150054 |

Features

| | |
|-----------------|----------|
| Ballast Type | N/A |
| beam angle | 240 Deg |
| Circuit Type | N/A |
| Input Voltage | 120-277V |
| ip rating | N/A |
| lumens | 2600 |
| Nominal Length | 48 in |
| Nominal Size | N/A |
| Number of Lamps | N/A |
| Output Current | N/A |
| Output Voltage | N/A |
| Sensor Type | N/A |
| Warranty | 5 |
| Wattage | 18.5 |
| Wire Type | N/A |

Material, Color, and Finish

| | |
|-----------------------------|---------|
| Base Type | G13 |
| color rendering index (cri) | >80 Deg |
| color temperature | 5000 |
| housing color | N/A |

Descriptions

| | |
|------------------------|---|
| Construction | Frosted Shatterproof Glass |
| Description | 18.5W LED T8 48" 50K LINE DBL/SNGL ENDED GC 2600LM |
| extra long description | Key KT-LED18.5T8-48GC-850-DX2 /G2-C |
| Long Description | 18.5W LED T8 Tube, Glass Construction, 4ft, 5000K, 120-277V Input, 25 pcs Carton, Direct Drive Single or Double Ended. Gen.2 |
| Product Type | 18.5W, 2600 Lumen, 4' 240' Beam Angle, Ballast Bypass, DLC 4 |



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Manufacturer Information

| | |
|---------------------------|--------------------------------|
| Brand | Keystone |
| GTIN | 00843654120966 |
| Manufacturers Part Number | KT-LED18.5T8-48GC-850-DX2 /G2- |
| UPC | 843654120966 |

Taxonomies, Classifications, and Categories

| | |
|----------------------|--|
| Category Description | LED LINEAR STRAIGHT(Fluor replacement), U-SHAPE & CIRCULAR LAMPS |
|----------------------|--|

Packaging

| | |
|-----------------|------|
| Carton | 25 |
| Weight Per each | 0.66 |

Uses, Certifications, and Standards

| | |
|-------------|---|
| Energy Star | N |
|-------------|---|