



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



L2130R Turnlok SGL Recp 5W 30A 3P 120/208V

Pass & Seymour/Legrand

| | |
|------------------|---|
| Catalog Number | L2130R |
| Manufacturer | Pass & Seymour/Legrand |
| Description | Turnlok Registered Single Receptacle 5-Wire 30A 3-Phase 120/208V |
| Weight per unit | 0.2500 (lbs/each) |
| Product Category | Gen Purpose Recept & Surge Pro |

Features

| | |
|-----------------|---------|
| amperage rating | 30 |
| Material | Nylon |
| Number of Wires | 3 |
| Poles | 2 |
| Voltage | 120.0 V |
| Voltage Rating | 120/208 |
| Wire Size | 4 |

Material, Color, and Finish

| | |
|-------|-------|
| Color | Black |
|-------|-------|

Dimensions and Weight

| | |
|------|--------|
| Size | 3.3 in |
|------|--------|

Descriptions

| | |
|------------------------|---|
| Description | TURNLOK SGL RECP 5W 30A 3P 120/208V |
| extra long description | P&S L2130R TURNLOK SGL REC 5W 30A 3 |
| Long Description | Turnlok Registered Single Receptacle 5-Wire 30A 3-Phase 120/208V |
| Product Type | Turnlok SGL Rec 5W 30A 3P 120/208V |
| Special Features | Locking Device, impact resistant |

Manufacturer Information

| | |
|---------------------------|------------------|
| Brand | Pass and Seymour |
| GTIN | 00785007213058 |
| Manufacturers Part Number | L2130-R |
| UPC | 785007213058 |

Taxonomies, Classifications, and Categories

| | |
|----------------------|----------------------------|
| Category Description | Residential receptacles |
| Type | Turnlock Single Receptacle |

Trade Size

| | |
|----------|------|
| Amperage | 30.0 |
|----------|------|



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Packaging

| | |
|-----------------|------|
| Carton | 1 |
| Package | 50 |
| Weight Per each | 0.25 |

Uses, Certifications, and Standards

| | |
|-------------|---------------------------------|
| Application | Industrial Spec Grade |
| Mounting | Receptacle |
| nema rating | L21-30R |
| standard | FEDSPEC, CULUS, UL 498, FEDSPEC |