



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## L75058 750 5/8" 1 Hole Compression Lug

*Nsi Industries*

Catalog Number	L75058
Manufacturer	Nsi Industries
Description	1 Hole Long Barrel Copper Compression Lug 750 MCM - 5/8" Bolt Long Barrel Copper Compression Lugs Are Produced From High Conductivity Copper Tubing. They Are Tin-Plated to Provide Corrosion Low Contact Resistance. Marked With Die Index and Color Coded For Easy Reference. Listed For 35KV Maximum When Properly Installed and to Cable Manufacturer Instructions. Temperature Rating 90 Degrees C. .
Weight per unit	0.9600 (lbs/each)
Product Category	Large Terminals & Connectors

### Features

Cable Size	750 MCM (STR)
Material	Copper
Number of Holes	1
Stud Size	5/8
Voltage Rating	600 V
Warranty	1 YEAR

### Material, Color, and Finish

Color	Black
Finish	Tin Plated

### Dimensions and Weight

Size	L=5.15 - W=1.90 - OD=1.31 - ID=1.03
------	-------------------------------------



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Descriptions

Description	750 5/8" 1 HOLE COMPRESSION LUG
extra long description	NSI L75058 CU CMP Lug Long 750 MCM
Features	1 Hole Long Barrel Copper Compression Lug 750 MCM - 5/8" Bolt Long Barrel Copper Compression Lugs are produced from high conductivity copper tubing. They are tin-plated to provide corrosion low contact resistance. Marked with die index and color coded for easy reference. Listed for 35KV maximum when properly installed and to cable manufacturer instructions. Temperature rating 90 degrees C. .
Long Description	1 Hole Long Barrel Copper Compression Lug 750 MCM - 5/8" Bolt Long Barrel Copper Compression Lugs are produced from high conductivity copper tubing. They are tin-plated to provide corrosion low contact resistance. Marked with die index and color coded for easy reference. Listed for 35KV maximum when properly installed and to cable manufacturer instructions. Temperature rating 90 degrees C. .
Product Type	Cu CMP Lug Long 750 MCM 5/8 Bolt Size
Special Features	750 MCM (STR) - 5/8 Mounting Hole

## Manufacturer Information

Brand	NSi
GTIN	00662381034199
Manufacturers Part Number	L75058
UPC	662381034199

## Taxonomies, Classifications, and Categories

Category Description	Comp & Mech Lugs and Butt Splices
Type	Long Barrel - One Hole

## Packaging

Carton	1
Package	3
Weight Per each	0.96

## Uses, Certifications, and Standards

Application	Terminate, Splice, Tap Power Connectors
environmental conditions	90 C
Mounting	5/8 Mounting Hole
standard	UL486A/B