



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## L750N 750 1/2" 2 Hole Long Barrel Compression Lug

*Nsi Industries*

Catalog Number	L750N
Manufacturer	Nsi Industries
Description	2 Hole Long Barrel Copper Compression Lug 750 MCM-1/2" Bolt - 1 3/4" Mounting Hole Spacing Long Barrel Copper Compression Lugs Is A Type Of Copper Compression Connector That Is Produced From High Conductivity Copper Tubing. They Are Tin-Plated to Provide Corrosion Resistance and Are Marked With Die Index and Color Coded For Easy Reference. Listed For 35KV Maximum When Properly Installed.
Weight per unit	1.2 (lbs/each)
Product Category	Large Terminals & Connectors

### Features

Cable Size	750 MCM (STR)
Material	Copper
Number of Holes	2
Stud Size	1/2
Voltage Rating	600 V
Warranty	1 YEAR

### Material, Color, and Finish

Color	Black
Finish	Tin Plated

### Dimensions and Weight

Size	L=6.30 - W=1.90 - OD=1.31 - ID=1.04
------	-------------------------------------



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Descriptions

Description	750 1/2" 2 HOLE LONG BARREL COMPRESSION LUG
extra long description	NSI L750N CU CMP Lug Long 750 MCM N
Features	2 Hole Long Barrel Copper Compression Lug 750 MCM-1/2" Bolt - 1 3/4" Mounting Hole Spacing Long Barrel Copper Compression Lugs is a type of copper compression connector that is produced from high conductivity copper tubing. They are tin-plated to provide corrosion resistance and are marked with die index and color coded for easy reference. Listed for 35KV maximum when properly installed.
Long Description	2 Hole Long Barrel Copper Compression Lug 750 MCM-1/2" Bolt - 1 3/4" Mounting Hole Spacing Long Barrel Copper Compression Lugs is a type of copper compression connector that is produced from high conductivity copper tubing. They are tin-plated to provide corrosion resistance and are marked with die index and color coded for easy reference. Listed for 35KV maximum when properly installed.
Product Type	Cu CMP Lug Long 750 MCM Nema MTG Spac
Special Features	750 MCM (STR) - 1/2 Mounting Hole - 1 3/4 Hole Spacing

## Manufacturer Information

Brand	NSi
GTIN	00662381035196
Manufacturers Part Number	L750N
UPC	662381035196

## Taxonomies, Classifications, and Categories

Category Description	Comp & Mech Lugs and Butt Splices
Type	Long Barrel - Two Hole

## Packaging

Carton	1
Package	3
Weight Per each	1.15

## Uses, Certifications, and Standards

Application	Terminate, Splice, Tap Power Connectors
environmental conditions	90 C
Mounting	1/2 Mounting Holes
standard	UL486A/B