



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



LED13WA190MN840D 13W Led A19 40K Dim Omni-Directional

Eiko LTD

| | |
|------------------|---|
| Catalog Number | LED13WA190MN840D |
| Manufacturer | Eiko LTD |
| Description | Features: Led A19 13W-1600LM Dim Enclosed 80+Cri 4000K E26 120 Vac |
| Weight per unit | 0.1900 (lbs/each) |
| Product Category | Lighting |

Features

| | |
|----------------|--------------------|
| average life | 25,000 |
| Base | Medium Screw (E26) |
| beam angle | 240° |
| lumens | 1,600 |
| Shape | A19 |
| Voltage Rating | 120 |
| Wattage | 13 |

Material, Color, and Finish

| | |
|-----------------------------|------|
| Color | K |
| color rendering index (cri) | 80+ |
| color temperature | 4000 |

Dimensions and Weight

| | |
|------|-----------------|
| Size | 2.36 DIA X 4.60 |
|------|-----------------|

Descriptions

| | |
|------------------------|---|
| Description | 13W LED A19 40K DIM OMNI-DIRECTIONAL |
| extra long description | EIKO LED13WA19/OMN/840-DIM-B LED A1 |
| Long Description | Features: LED A19 13W-1600LM DIM ENCLOSED 80+CRI 4000K E26 120 VAC |
| Product Type | Led A19 13W-1600LM Dim Enclosed 80+Cri 4 |

Manufacturer Information

| | |
|---------------------------|-------------------------|
| Brand | Eiko |
| GTIN | 00031293110909 |
| Manufacturers Part Number | LED13WA19/OMN/840-DIM-B |
| UPC | 031293110909 |

Taxonomies, Classifications, and Categories

| | |
|----------------------|------------------------|
| Category Description | LED A-LINE SHAPE LAMPS |
|----------------------|------------------------|

Packaging

| | |
|-----------------|------|
| Carton | 1 |
| Weight Per each | 0.19 |



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Uses, Certifications, and Standards

standard

cULus, Energy Star, RoHS
