



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



LED27HIDEX39850D 27W Led Hid RPL 50K 120-277V *Keystone Technologies*

| | |
|------------------|---|
| Catalog Number | LED27HIDEX39850D |
| Manufacturer | Keystone Technologies |
| Description | Led Lamp, Non-Dimmable, Hid Replacement Led, 1ST Generation, Instant Start Type; 8.35 Inch; UI (Canada and Us), DLC Approval; Enclosed Fixture Application; 120 to 277 Volt Ac Voltage Rating; 3.43 Inch Diameter |
| Weight per unit | 1.9 (lbs/each) |
| Product Category | Led Specialty Lamps & Modules |

Features

| | |
|----------------|---|
| Current Rating | 0.23 Amp at 120 Volt AC, 0.1 Amp at 277 Volt AC |
| Intensity | 3830 Lumen |
| Item | LED Lamp |
| Voltage Rating | 120 to 277 Volt AC |
| Wattage | 27 Watt |

Material, Color, and Finish

| | |
|-----------------------------|------------|
| Base Type | Ex39 Mogul |
| Color Rendering Index | 83 |
| Color Temperature in Kelvin | 5000 |

Dimensions and Weight

| | |
|----------|-----------|
| Diameter | 3.43 INCH |
| Length | 8.35 Inch |

Descriptions

| | |
|------------------------|---|
| Additional Information | RoHS Compliant; Equivalent Wattage 100 Watt; Efficacy 142 Lumen per Watt; Enclosure IP64; Visible Light Area 360 Degree; Temperature -20 to 140 Deg F |
| Commodity Description | LED SPECIALTY LAMPS & MODULES |
| Description | 27W LED HID RPL 50K 120-277V |
| Long Description | LED LAMP, NON-DIMMABLE, HID REPLACEMENT LED, 1ST GENERATION, INSTANT START TYPE; 8.35 INCH; UL (CANADA AND US), DLC APPROVAL; ENCLOSED FIXTURE APPLICATION; 120 TO 277 VOLT AC VOLTAGE RATING; 3.43 INCH DIAMETER |
| Product Type | Led Lamp |



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Manufacturer Information

| | |
|---------------------------|------------------------|
| Brand | Keystone Technologies |
| Manufacturers Part Number | KT-LED27HID-EX39-850-D |
| Model | 800 |

Taxonomies, Classifications, and Categories

| | |
|----------------------|--|
| Category Description | LED SPECIALTY LAMPS & MODULES |
| Type | Non-Dimmable, HID Replacement LED, 1st Generation, Instant Start |

Packaging

| | |
|-----------------|------|
| Carton | 1 |
| Weight Per each | 1.93 |

Uses, Certifications, and Standards

| | |
|-------------|-------------------------|
| Application | Enclosed Fixture |
| Approval | UL (Canada and US), DLC |