



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



LED6MR16DIM830NF 6W Led MR16 30K 450LM 25D *Sylvania-Ledvance*

| | |
|------------------|---|
| Catalog Number | LED6MR16DIM830NF |
| Manufacturer | Sylvania-Ledvance |
| Description | Led MR16, 6W, Dimmable, 83CRI, 450 Lumen, 3000K, 25000 Life |
| Weight per unit | 0.1850 (lbs/each) |
| Product Category | Led Reflector Gu, MR R Shape L |

Features

| | |
|----------------|-------------|
| average life | 25000 |
| Base | GU5.3 Bipin |
| Lamp Type | LED MR16 |
| lumens | 450 |
| Shape | MR16 |
| Voltage | 12.00 V |
| Voltage Rating | 12.00 |
| Wattage | 5.00 |

Material, Color, and Finish

| | |
|-----------------------------|----------------|
| color rendering index (cri) | 83 |
| Style | MR16 reflector |

Dimensions and Weight

| | |
|------|------|
| Size | 1.97 |
|------|------|

Descriptions

| | |
|------------------------|---|
| Description | 6W LED MR16 30K 450LM 25D |
| extra long description | SYL LED6MR16DIM830NFL25GLRP/78240 L |
| Long Description | LED MR16, 6W, Dimmable, 83CRI, 450 Lumen, 3000K, 25000 life |
| Product Type | LED6MR16DIM830NFL25GLRP 6/CS 1/Sku |

Manufacturer Information

| | |
|---------------------------|-------------------------------|
| Brand | SYLVANIA |
| GTIN | 00046135782404 |
| Manufacturers Part Number | LED6MR16DIM830NFL25GLRP/78240 |
| UPC | 046135782404 |

Taxonomies, Classifications, and Categories

| | |
|----------------------|------------------------------------|
| Category Description | LED REFLECTOR GU, MR R SHAPE LAMPS |
|----------------------|------------------------------------|

Packaging

| | |
|-----------------|-------|
| Carton | 1 |
| Package | 6 |
| Weight Per each | 0.185 |



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Uses, Certifications, and Standards

standard

RoHS
