



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



LED18T8U6GC850D 18W Led T8 U-Bend 6" 50K Line Voltage

Keystone Technologies

| | |
|------------------|---|
| Catalog Number | LED18T8U6GC850D |
| Manufacturer | Keystone Technologies |
| Description | 18W Led T8 Tube. Shatter-Proof Coated Glass, 120-277V Input: Direct Drive, 6" U-Bend, 5000K, 12 PCS Carton, Carton Pack |
| Weight per unit | 0.5100 (lbs/each) |
| Product Category | Shape & Circular Lamps |

Features

| | |
|-----------------|----------|
| Ballast Type | N/A |
| beam angle | 240 Deg |
| Circuit Type | N/A |
| Input Voltage | 120-277V |
| ip rating | N/A |
| lumens | 2150 |
| Nominal Length | 6 U-Bend |
| Nominal Size | N/A |
| Number of Lamps | N/A |
| Output Current | N/A |
| Output Voltage | N/A |
| Sensor Type | N/A |
| Wattage | 18 |
| Wire Type | N/A |

Material, Color, and Finish

| | |
|-----------------------------|---------|
| Base Type | G13 |
| color rendering index (cri) | >80 Deg |
| color temperature | 5000 |
| housing color | N/A |

Descriptions

| | |
|------------------------|---|
| Construction | Frosted Glass |
| Description | 18W LED T8 U-BEND 6" 50K LINE VOLTAGE |
| extra long description | Key KT-LED18T8-U6GC-850-D-CP 18W, 2 |
| Long Description | 18W LED T8 Tube. Shatter-Proof Coated Glass, 120-277V Input: Direct Drive, 6" U-Bend, 5000K, 12 pcs Carton, Carton Pack |
| Product Type | 18W, 2200 Lumen, 6" U-Bend, 220' Beam Angle, Ballast Bypass, |

Manufacturer Information

| | |
|---------------------------|--------------------------|
| Brand | Keystone |
| GTIN | 00890949012536 |
| Manufacturers Part Number | KT-LED18T8-U6GC-850-D-CP |
| UPC | 890949012536 |



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Taxonomies, Classifications, and Categories

| | |
|----------------------|--|
| Category Description | LED LINEAR STRAIGHT(Fluor replacement), U-SHAPE & CIRCULAR LAMPS |
|----------------------|--|

Packaging

| | |
|--------|----|
| Carton | 12 |
|--------|----|

| | |
|-----------------|------|
| Weight Per each | 0.51 |
|-----------------|------|

Uses, Certifications, and Standards

| | |
|-------------|---|
| Energy Star | N |
|-------------|---|