



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



LL125DCG 1.25" Cond Body C/G

Appleton/Oz Gedney

Catalog Number	LL125DCG
Manufacturer	Appleton/Oz Gedney
Description	Emt Conduit Bodies, Type:Threaded Conduit, Material: Diecast Aluminum/ Epoxy Powder Coat, UI Standard: 514A, Trade Size 1 1/4, Dimension: Length 7.87 Inches, Width 3.50 Inches, Height 2.97 Inches
Weight per unit	2.0 (lbs/each)
Product Category	Alum

Material, Color, and Finish

Finish	Epoxy Powder Coat;Other
--------	-------------------------

Dimensions and Weight

Height	2.97
Hub Size	1-1/2
Length	7.87
Width	3.5

Descriptions

Description	1.25" COND BODY C/G
extra long description	EGS LL125DCG 1-1/4 THD ALUM LL BDY
Long Description	EMT Conduit Bodies, Type:Threaded Conduit, Material: Diecast Aluminum/ Epoxy Powder Coat, UL Standard: 514A, Trade Size 1 1/4, Dimension: Length 7.87 Inches, Width 3.50 Inches, Height 2.97 Inches
Product Type	1-1/4 THD Alum LL Bdy CVR GSKT
Special Features	1-1/4 IN Trade Size, Type LL Aluminum Threaded Conduit Body, Maximum No. of Conductors 3 - #2 AWG, Volume 35.40 IN ³ , For Use With Rigid and IMC Conduit, Furnished With Stamped Aluminum Cover and Neoprene Gasket

Manufacturer Information

Brand	Appleton
GTIN	00687855000715
Manufacturers Part Number	LL125DCG
UPC	687855000715

Taxonomies, Classifications, and Categories

Category Description	FORM 5 CONDULETS, COVERS, & GASKETS
Type	Conduit Body



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Packaging

Carton	20
Weight Per each	2

Uses, Certifications, and Standards

Application	Provides access to the interior of the raceway for wire pulling , splicing and maintenance, Allows connection of straight and branch conduit runs and 90 degree bends
standard	CSA Certified: 208044;CSA Standard: C22.2 No. 18.3;NEMA: FB-1;UL Listed: E53330;UL Standard: 514A