




## FLUORESCENT LIGHT FIXTURE HANGER, TOP MOUNT

### CATALOG NUMBER

**LFC90**



### FEATURES

Provides an easy method of supporting an industrial class fluorescent light fixture from S-Hooks and Jack Chain

Fits most fluorescent light fixtures

Reduces the need to modify Jack Chain for fixture installation

No tools required for installation

### PRODUCT ATTRIBUTES

Material: Steel

Finish: Plain

Orientation: Top Mount

Static Load: 50lb

### WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at [www.nvent.com](http://www.nvent.com) and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

#### North America

+1.800.753.9221

Option 1 – Customer Care

Option 2 – Technical Support

#### Europe

Netherlands:

+31 800-0200135

France:

+33 800 901 793

#### Europe

Germany:

800 1890272

Other Countries:

+31 13 5835404

#### APAC

Shanghai:

+ 86 21 2412 1618/19

Sydney:

+61 2 9751 8500




Our powerful portfolio of brands:  
**nVent.com CADDY ERICO HOFFMAN RAYCHEM SCHROFF**  
**TRACER**



## FLUORESCENT LIGHT FIXTURE HANGER, TOP MOUNT

### CATALOG NUMBER

**LFC90**



### FEATURES

Provides an easy method of supporting an industrial class fluorescent light fixture from S-Hooks and Jack Chain

Fits most fluorescent light fixtures

Reduces the need to modify Jack Chain for fixture installation

No tools required for installation

### PRODUCT ATTRIBUTES

Material: Steel

Finish: Plain

Orientation: Top Mount

Static Load: 50lb

### WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at [www.nvent.com](http://www.nvent.com) and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

#### North America

+1.800.753.9221

Option 1 – Customer Care

Option 2 – Technical Support

#### Europe

Netherlands:

+31 800-0200135

France:

+33 800 901 793

#### Europe

Germany:

800 1890272

Other Countries:

+31 13 5835404

#### APAC

Shanghai:

+ 86 21 2412 1618/19

Sydney:

+61 2 9751 8500



Our powerful portfolio of brands:  
**nVent.com CADDY ERICO HOFFMAN RAYCHEM SCHROFF**  
**TRACER**