



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



LKPC100 1" LKG Cobra Clamp Emt/Rigid

Abb Installation Products, Inc

| | |
|------------------|---|
| Catalog Number | LKPC100 |
| Manufacturer | Abb Installation Products, Inc |
| Description | Clamp, One-Piece, Emt and Rigid Conduit Trade Size 1 Inch, Cable Outer Diameter Range 1.100-1.400 Inch, Steel |
| Weight per unit | 0.2000 (lbs/each) |
| Product Category | Channel & Strut Fittings |

Features

| | |
|----------|-------|
| Material | Steel |
|----------|-------|

Material, Color, and Finish

| | |
|--------|-------------------|
| Finish | GoldGalv/Standard |
|--------|-------------------|

Dimensions and Weight

| | |
|------|--------|
| Size | 1 INCH |
|------|--------|

Descriptions

| | |
|------------------------|---|
| Also Known As... | Strut Clamp Pipe Clamp for Strut Conduit/Pipe Clamp for Strut Strut Strap |
| Description | 1" LKG COBRA CLAMP EMT/RIGID |
| extra long description | ABB LKPC100 STRUT LOC-KING COBRA C |
| Long Description | Clamp, One-Piece, EMT and Rigid Conduit Trade Size 1 Inch, Cable Outer Diameter Range 1.100-1.400 Inch, Steel |
| Product Type | Strut Loc-King Cobra Clamp 1 In |
| Special Features | Safety Factor = 4 |

Manufacturer Information

| | |
|---------------------------|---------------------------|
| Brand | Thomas&Betts-Abb Ins Prod |
| GTIN | 00616013120347 |
| Manufacturers Part Number | LKPC100 |
| UPC | 616013120347 |

Taxonomies, Classifications, and Categories

| | |
|----------------------|--------------------------------------|
| Category Description | STRUT STRAPS |
| Type | Pipe Straps, Pipe Clamps and Hangers |

Packaging

| | |
|-----------------|-----|
| Carton | 100 |
| Weight Per each | 0.2 |



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Uses, Certifications, and Standards

| | |
|-------------|-------------------------|
| Application | For conduits and cables |
| standard | UL E160899 / UL E160899 |