



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

3705 Lee Street  
71302-0000, LA Alexandria  
Phone: 318-445-1336  
Fax: 318-445-8356



## LR100DCG 1" LR Condulet W/C&G *Appleton/Oz Gedney*

Catalog Number	LR100DCG
Manufacturer	Appleton/Oz Gedney
Description	Features:With Cover, Gasket, Standard:UL 514A, Csa C22.2, Nema FB-1, Nema FB-2.10, Fed Spec A-A-50563, Hub Size:1IN, Form:LR, Length:5.94IN, Width:2.68IN, Height:2.14IN, Material:Die-Cast Copper Free Aluminum, Finish:Powder Coated
Weight per unit	0.6000 (lbs/each)
Product Category	Alum

### Features

Connector Type	Compression
Form	LR

### Material, Color, and Finish

Finish	Powder Coated
--------	---------------

### Dimensions and Weight

Height	2.14
Hub Size	1
Length	5.94
Width	2.68

### Descriptions

Description	1" LR CONDULET W/C&G
extra long description	EGS LR100DCG 1 IN THD ALUM LR BDY C
Long Description	Features:With Cover, Gasket, Standard:UL 514A, CSA C22.2, NEMA FB-1, NEMA FB-2.10, Fed Spec A-A-50563, Hub Size:1IN, Form:LR, Length:5.94IN, Width:2.68IN,Height:2.14IN, Material:Die-Cast Copper Free Aluminum, Finish:Powder Coated
Product Type	1 In THD Alum LR Bdy CVR GSKT
Special Features	With Cover and Gasket

### Manufacturer Information

Brand	Appleton
GTIN	00687855000760
Manufacturers Part Number	LR100DCG
UPC	687855000760

### Taxonomies, Classifications, and Categories

Category Description	FORM 5 CONDULETS, COVERS, & GASKETS
Type	Conduit Body Rigid Threaded

### Trade Size

Trade Size	4
------------	---



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

3705 Lee Street  
71302-0000, LA Alexandria  
Phone: 318-445-1336  
Fax: 318-445-8356

## Packaging

Carton	5
Package	20
Weight Per each	0.6

## Uses, Certifications, and Standards

Application	Provides access to the interior of the raceway for wire pulling , splicing and maintenance, Allows connection of straight and branch conduit runs and 90 degree bends
standard	UL 514A, CSA C22.2, NEMA FB-1, NEMA FB-2.10, Fed Spec A-A-50563