



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



M22DRPR MTN Mushroom PB Red

Eaton Corp

Catalog Number	M22DRPR
Manufacturer	Eaton Corp
Description	Eaton M22 Modular Pushbutton, M22 Modular Mushroom Pushbutton Operator, 22.5 MM, Maintained, Non-Illuminated, Bezel: Silver, Button: Red, IP67, IP69K, Nema 4X, 13, 1, 000, 000 Mechanical Operations
Weight per unit	0.0500 (lbs/each)
Product Category	Push Button Complete Assemblie

Features

action	Red
actuator	Mushroom
operating cycles	1 million

Dimensions and Weight

Depth	2
Height	1
Size	22.5 mm
Width	2

Descriptions

Description	MTN MUSHROOM PB RED
extra long description	ETN M22-DRP-R MTN MUSHROOM PB RED
Features	This attractive, functional line of pushbuttons features a space-saving construction that enables fast assembly. The complete illuminated M22 line offers LED light units to ensure high-quality brightness and up to 100,000 hours of illumination. Because of the rugged design of these pushbuttons, most operators and contact blocks exceed five million mechanical operations.
Long Description	Eaton M22 modular pushbutton, M22 Modular Mushroom Pushbutton Operator, 22.5 mm, Maintained, Non-illuminated, Bezel: Silver, Button: Red, IP67, IP69K, NEMA 4X, 13, 1,000,000 mechanical operations
Product Type	MTN Mushroom PB Red

Manufacturer Information

Brand	EATON CUTLER-HAMMER
GTIN	00786685282718
Manufacturers Part Number	M22-DRP-R
Model	Modular pushbutton
UPC	786685282718



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Taxonomies, Classifications, and Categories

Category Description MINATURE PILOT DEVICES.22MM

Packaging

Carton 1

Weight Per each 0.05

Uses, Certifications, and Standards

Application Stationary Machinery and Equipment Outside Factory -
..... Stationary Machinery and Equipment Outside Factory - Other

environmental conditions IP67, IP69K

standard CSA Certified,CCC Marked,Lloyd's Register
..... Certified,GoST-R,Bureau Veritas,CE Marked