



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## LTXES04BC 1"X100' LT Flex Metallic Conduit

*Abb Installation Products, Inc*



Catalog Number	LTXES04BC
Manufacturer	Abb Installation Products, Inc
Description	Liquid Tight Flexible Metallic Conduit, Extreme Temperature Range, Galvanised Steel Core With TPR Jacket, Conduit Size 1 Inch, Length 30 Meters/100 Feet, Working Temperature -60 to 150 Degrees C, Intermitting to 165 Degrees C, Compliant to Rohs, Black
Weight per unit	0.5600 (lbs/each)
Product Category	Liquid Tight Conduit

### Features

Inside Diameter	1.041
outside diameter	1.315

### Material, Color, and Finish

Color	Black
Finish	TPR Jacket

### Dimensions and Weight

Length	1200
--------	------

### Descriptions

Description	1"X100' LT FLEX METALLIC CONDUIT
extra long description	ABB LTXES04B-C LFMC XTMP 1IN BLK 30
Features	Extreme temperature, CE compliant Liquid-tight FlexibleMetallic Conduits provide excellent performance inextreme low and high temperature environments
Long Description	Liquid Tight Flexible Metallic Conduit, Extreme Temperature Range, Galvanised Steel Core with TPR Jacket, Conduit Size 1 Inch, Length 30 Meters/100 Feet, Working Temperature -60 to 150 Degrees C, Intermitting to 165 Degrees C, Compliant to RoHS, Black
Product Type	LFMC XTMP 1IN BLK 30M/100FT
Special Features	Designed to meet UL 360 ID/OD dimension requirements

### Manufacturer Information

Brand	T&B Liquidtight Systems
GTIN	00786210106724
Manufacturers Part Number	LTXES04B-C
UPC	786210106724



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Taxonomies, Classifications, and Categories

Category Description	Liquid Tight
Type	Liquid Tight Flexible Metallic Conduit

## Trade Size

Trade Size	1 in
------------	------

## Availability

minimum qty	100
-------------	-----

## Packaging

Carton	100
Weight Per foot	0.56

## Uses, Certifications, and Standards

Application	Used in extremely high temperature applications such as commercial ovens and refrigeration, industrial furnaces and foundries
standard	RoHS