



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## MC1020RGYGN 10/2 WG MC Sol or/Gy/GN Alu Armor *Southwire Company*

Catalog Number	MC1020RGYGN
Manufacturer	Southwire Company
Description	10-2 Solid Orange, Gray, Green - MC Tuff®, Blue Interlocked Lightweight Galvanized Steel Armor With Phase Id - Type MC - 250' Coil
Weight per unit	0.1600 (lbs/ft)
Product Category	Teck

### Features

Bend Radius	8.73
Conductor Size	10
gauge	10 AWG
Inside Diameter	0.382
Material	Galvanized Steel
Number of Conductors	3
outside diameter	0.582
Voltage Rating	600V

### Material, Color, and Finish

Conductor Material	Copper
Finish	Blue Paint
Insulation Material	THHN

### Dimensions and Weight

Length	3000
--------	------



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Descriptions

Description	10/2 WG MC SOL OR/GY/GN ALU ARMOR
extra long description	AFC 1707B42T02 10-2 MCS 250C
Features	MC Tuff is a lightweight, high-strength Type MC Cable with blue galvanized steel interlocked armor that features ColorSpec®ID/ColorTrak® ID for easy identification. MC Tuff cables meet UL Standard 1569 and NEC 330, have no conductor count limit, and offer various conductor bundle combinations. These bundles consist of THHN/THWN rated conductors that are twisted and wrapped with polypropylene assembly tape. They also come with an insulated green equipment grounding conductor. Additionally, Atkore offers a G
Long Description	10-2 Solid Orange, Gray, Green - MC Tuff®, Blue Interlocked Lightweight Galvanized Steel Armor with phase ID - Type MC - 250' Coil
Product Type	10-2 MCS 250C
Short Description	10-2 MCS 250C
Special Features	Galvanized interlocking steel strip, utilizes ColorSpec® ID system

## Manufacturer Information

Brand	Flexible Conduit
GTIN	00077680195784
Manufacturers Part Number	1707B42T02
UPC	077680195784

## Taxonomies, Classifications, and Categories

Category Description	BX & MC
Type	MC Tuff® Lightweight Steel Cable

## Trade Size

Trade Size	10-2
------------	------

## Availability

Status	Inactive
--------	----------

## Packaging

Carton	250
Weight	1192.224
Weight Per foot	0.16

## Uses, Certifications, and Standards

Temperature Rating	194
--------------------	-----