




**NON-METALLIC LOW PROFILE WIU COVERS**

**Two Gang Flat Expandable While-In-Use Covers  
2-Gang 55-in-1**

**C07**



Catalog #: ML2450G

**APPLICATIONS**

Low profile design that is expandable for weatherproof protection while an outlet is in use.  
N/A

**PRODUCT FEATURES**

Revolutionary patented design expands from 1" to 3" for while-in-use needs  
100% paintable surface  
Ultra rugged polycarbonate & synthetic neoprene rubber that will not dry rot, crack or deteriorate in sunlight  
Patented Quick-Fit™ keyhole mounting system allows installation in under a minute.  
Includes attached gasket and mounting hardware

**UL LISTED**

File E116141

**NEMA**

3R Rated

**NEC**

2014 Compliant (article 406.9A)

**US PATENTS**

8,101,861; 8,319,334; 8,053,671

**GENERAL PRODUCT INFORMATION**

Color: Gray

**CONFIGURATION**

Gangs: 2

**PRODUCT MEASUREMENTS**

Depth: 1 in. to 3 in.  
Wt. Ea. (Lbs.): 0.710

**PACKAGING**


Package Type: Shrink  
Std. Pkg.: 10  
Product UPC-A Labeled: Yes  
Weight (Lbs. Per/C): 71.00  
Ship Carton Length (in.): 7.88  
Ship Carton Width (in.): 6.25  
Ship Carton Height (in.): 6.63  
Ctn Weight (Lbs.): 4.26  
Pallet Qty: 1296.00  
UPC Number: 050169917350  
I2of5: 50050169917355



**NON-METALLIC LOW PROFILE WIU COVERS**

**Two Gang Flat Expandable While-In-Use Covers  
2-Gang 55-in-1**

**C07**



Catalog #: ML2450G

**APPLICATIONS**

Low profile design that is expandable for weatherproof protection while an outlet is in use.  
N/A

**PRODUCT FEATURES**

Revolutionary patented design expands from 1" to 3" for while-in-use needs  
100% paintable surface  
Ultra rugged polycarbonate & synthetic neoprene rubber that will not dry rot, crack or deteriorate in sunlight  
Patented Quick-Fit™ keyhole mounting system allows installation in under a minute.  
Includes attached gasket and mounting hardware

**UL LISTED**

File E116141

**NEMA**

3R Rated

**NEC**

2014 Compliant (article 406.9A)

**US PATENTS**

8,101,861; 8,319,334; 8,053,671

**GENERAL PRODUCT INFORMATION**

Color: Gray

**CONFIGURATION**

Gangs: 2

**PRODUCT MEASUREMENTS**

Depth: 1 in. to 3 in.  
Wt. Ea. (Lbs.): 0.710

**PACKAGING**

Package Type: Shrink  
Std. Pkg.: 10  
Product UPC-A Labeled: Yes  
Weight (Lbs. Per/C): 71.00  
Ship Carton Length (in.): 7.88  
Ship Carton Width (in.): 6.25  
Ship Carton Height (in.): 6.63  
Ctn Weight (Lbs.): 4.26  
Pallet Qty: 1296.00  
UPC Number: 050169917350  
I2of5: 50050169917355