



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



MMX34AA9D0F00 M-Max 3P 480V In/3P 480V Out 9.0A 5.0HP FS3 W Emc Eaton Corp

Catalog Number	MMX34AA9D0F00
Manufacturer	Eaton Corp
Description	Eaton M-Max Series Adjustable Frequency Ac Drives Basic Controller, Full Version, AA Software Design Series, Emc Filter, FS3 Frame, 380-480V, 460V, IP20 Enclosure Rating, 5 HP, 9A Output, 11.5A Input, Three-Phase In, Three-Phase Out
Weight per unit	3.0 (lbs/each)
Product Category	Ac Drives

Features

dimensions	3.9400 IN X 5.5000 IN X 4.2700 IN
Output Current	9 A

Descriptions

Description	M-MAX 3P 480V IN/3P 480V OUT 9.0A 5.0HP FS3 W EMC
extra long description	ETN MMX34AA9D0F0-0 MMX 480V,9.0A,5.
Features	Demand more simplicity. The M-Max series of variable frequency drive is a compact system with a broad power range. Factor in the conformal board coating, unique mounting characteristics, simple programming, and its 50°C Rating and the M-Max is perfectly suited for machinery applications in many industries including material handling, HVAC, pumping and more.
Long Description	Eaton M-Max Series Adjustable Frequency AC Drives Basic Controller, Full version, AA software design series, EMC filter, FS3 frame, 380-480V, 460V, IP20 enclosure rating, 5 hp, 9A output, 11.5A input, Three-phase in, three-phase out
Product Type	MMX 480V, 9.0A, 5.0HP, FS3, W Emc
Special Features	Aa Software Design Series, Emc Filter

Manufacturer Information

Brand	EATON CUTLER-HAMMER
GTIN	00786685268842
Manufacturers Part Number	MMX34AA9D0F0-0
UPC	786685268842

Taxonomies, Classifications, and Categories

Category Description	DRIVES
Type	Sensorless vector adjustable frequency drive

Packaging

Carton	1
Weight Per each	3



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Uses, Certifications, and Standards

Application

Elec Assemblies, Panels & OEM - Electrical Assemblies and
OEMs - Other

standard

UL Listed,EN 61800-3,EN 61800-5-1,EN 60204-1,cUL
Certified,C-Tick Compliant,EMC Category C2, C3, and C4 (Level
H): With an internal RFI filter option,RoHS Compliant,CE Marked