




TWO GANG MULTI-CONFIGURATION FLIP COVERS

**Two Gang Universal Metal Flip Covers
25-in-1**

D15



Catalog #: MX2050Z

APPLICATIONS

For use whenever weatherproof protection is required for an outdoor receptacle or switch.
N/A

PRODUCT FEATURES

- Heavy duty die-cast metal construction
- Patented Quick-Fit™ keyhole mounting system allows installation in under a minute.
- Pre-configured for GFCI with patented knockout technology for alternate devices
- Includes attached gasket and mounting hardware
- Premium powder coat finish
- Lockable tab

UL LISTED

File E212332

NEMA

3R Rated

NEC

2014 Compliant (article 406.9A)

US PATENTS

5,763,831; 6,420,653 B1; 6,420,654 B1; 4,874,906; 6,770,814 B2; 5,243,135; 6,642,453 B2; 6,441,307 B1; 6,563,051 B1; 6,559,381 B2; 6,723,922 B1; 6,700,063 B2

GENERAL PRODUCT INFORMATION

Color: Bronze

CONFIGURATION

Gangs: 2

PRODUCT MEASUREMENTS

Wt. Ea. (Lbs.): 0.485

PACKAGING


Package Type: Shrink
 Std. Pkg.: 4
 Product UPC-A Labeled: Yes
 Weight (Lbs. Per/C): 48.50
 Ship Carton Length (in.): 5.12
 Ship Carton Width (in.): 5.31
 Ship Carton Height (in.): 6.50
 Ctn Weight (Lbs.): 1.94
 Pallet Qty: 960.00
 UPC Number: 092326112802
 I2of5: 30092326112803



TWO GANG MULTI-CONFIGURATION FLIP COVERS

**Two Gang Universal Metal Flip Covers
25-in-1**

D15



Catalog #: MX2050Z

APPLICATIONS

For use whenever weatherproof protection is required for an outdoor receptacle or switch.
N/A

PRODUCT FEATURES

- Heavy duty die-cast metal construction
- Patented Quick-Fit™ keyhole mounting system allows installation in under a minute.
- Pre-configured for GFCI with patented knockout technology for alternate devices
- Includes attached gasket and mounting hardware
- Premium powder coat finish
- Lockable tab

UL LISTED

File E212332

NEMA

3R Rated

NEC

2014 Compliant (article 406.9A)

US PATENTS

5,763,831; 6,420,653 B1; 6,420,654 B1; 4,874,906; 6,770,814 B2; 5,243,135; 6,642,453 B2; 6,441,307 B1; 6,563,051 B1; 6,559,381 B2; 6,723,922 B1; 6,700,063 B2

GENERAL PRODUCT INFORMATION

Color: Bronze

CONFIGURATION

Gangs: 2

PRODUCT MEASUREMENTS

Wt. Ea. (Lbs.): 0.485

PACKAGING

Package Type: Shrink
 Std. Pkg.: 4
 Product UPC-A Labeled: Yes
 Weight (Lbs. Per/C): 48.50
 Ship Carton Length (in.): 5.12
 Ship Carton Width (in.): 5.31
 Ship Carton Height (in.): 6.50
 Ctn Weight (Lbs.): 1.94
 Pallet Qty: 960.00
 UPC Number: 092326112802
 I2of5: 30092326112803