



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



MSZ101IV Maestro DV 8A 0-10V Occupancy Ivory

Lutron

Catalog Number	MSZ101IV
Manufacturer	Lutron
Description	Maestro 0-10V Dimmer Occupancy/Vacancy Sensor, Passive Infrared, 8A Fluorescent Ballast or Led Driver, 120-277V, In Ivory
Weight per unit	0.4500 (lbs/each)
Product Category	Lighting Occupancy Sensors

Features

body	Plastic
load	8 A/0-10VDC
media	Yes
sensing range	900 ft ² (82 m ²) major motion coverage/400 ft ² (36 m ²) minor motion coverage
supply voltage	120 to 277

Material, Color, and Finish

Color	Ivory
Finish	Gloss



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Descriptions

Description	MAESTRO DV 8A 0-10V OCCUPANCY IVORY
extra long description	LUT MS-Z101-IV 0-10V DIMMER SENSOR
Features	The Lutron Maestro 0-10V Motion Sensor/Dimmer Switch works just like a Lutron Maestro dimmer with the addition of Lutron's advanced motion sensing technology to automatically and gradually turn the lights on and off. The 0-10V Motion Sensor/Dimmer Switch is rated to work with all drivers that provide a current source, up to 8A switching LED drivers and 50mA max sink current. Install in a single pole, 3-way with existing switch, or with Maestro companion switches (MA-AS/MS-AS) to switch from up to 9 locati
Long Description	Maestro 0-10V dimmer occupancy/vacancy sensor, passive infrared, 8A fluorescent ballast or LED driver, 120-277V, in ivory
Product Type	0-10V Dimmer Sensor Ivory
Special Features	Passive infrared sensors that automatically control the lights in an area. These sensors detect heat from occupants moving within an area to determine when the space is occupied. Combines a Maestro 0-10 V dimmer with an occupancy sensor. Controls 1-10 VDC electronic fluorescent ballast or LED driver load types. Passive infrared motion detection with exclusive Lutron XCT Technology for fine motion detection. 180 degree sensor field-of-view. Up to 30 ft x 30 ft (9 m x 9 m) [900 ft2 (81 m2)] major motion co

Manufacturer Information

Brand	Lutron
GTIN	00784276099868
Manufacturers Part Number	MS-Z101-IV
UPC	784276099868

Taxonomies, Classifications, and Categories

Category Description	Residential dimmers, motion sensors, controls, & photo cells
Type	Occupancy/Vacancy sensor dimmer, multi-location/3-way/single-pole, 0-10 V

Packaging

Carton	1
Weight Per each	0.45



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Uses, Certifications, and Standards

Application	Lighting Control
Enclosure	Plastic
environmental conditions	0 to 90% humidity, non-condensing. Indoor use only.
Mounting	WALLBOX
Operating Temperature	32 to 104
standard	UL, cUL, Title 20/24 certified