




TWO GANG MULTI-CONFIGURATION FLIP COVERS

**Two Gang Universal Metal Flip Covers
25-in-1**

D15



Catalog #: MX2050Z

APPLICATIONS

For use whenever weatherproof protection is required for an outdoor receptacle or switch.
N/A

PRODUCT FEATURES

Heavy duty die-cast metal construction
Patented Quick-Fit™ keyhole mounting system allows installation in under a minute.
Pre-configured for GFCI with patented knockout technology for alternate devices
Includes attached gasket and mounting hardware
Premium powder coat finish
Lockable tab

UL LISTED

File E212332

NEMA

3R Rated

NEC

2014 Compliant (article 406.9A)

US PATENTS

5,763,831; 6,420,653 B1; 6,420,654 B1; 4,874,906; 6,770,814 B2; 5,243,135; 6,642,453 B2; 6,441,307 B1; 6,563,051 B1; 6,559,381 B2; 6,723,922 B1; 6,700,063 B2

GENERAL PRODUCT INFORMATION

Color: Bronze

CONFIGURATION

Gangs: 2

PRODUCT MEASUREMENTS

Wt. Ea. (Lbs.): 0.485

PACKAGING


Package Type: Shrink
Std. Pkg.: 4
Product UPC-A Labeled: Yes
Weight (Lbs. Per/C): 48.50
Ship Carton Length (in.): 5.12
Ship Carton Width (in.): 5.31
Ship Carton Height (in.): 6.50
Ctn Weight (Lbs.): 1.94
Pallet Qty: 960.00
UPC Number: 092326112802
I2of5: 30092326112803



TWO GANG MULTI-CONFIGURATION FLIP COVERS

**Two Gang Universal Metal Flip Covers
25-in-1**

D15



Catalog #: MX2050Z

APPLICATIONS

For use whenever weatherproof protection is required for an outdoor receptacle or switch.
N/A

PRODUCT FEATURES

Heavy duty die-cast metal construction
Patented Quick-Fit™ keyhole mounting system allows installation in under a minute.
Pre-configured for GFCI with patented knockout technology for alternate devices
Includes attached gasket and mounting hardware
Premium powder coat finish
Lockable tab

UL LISTED

File E212332

NEMA

3R Rated

NEC

2014 Compliant (article 406.9A)

US PATENTS

5,763,831; 6,420,653 B1; 6,420,654 B1; 4,874,906; 6,770,814 B2; 5,243,135; 6,642,453 B2; 6,441,307 B1; 6,563,051 B1; 6,559,381 B2; 6,723,922 B1; 6,700,063 B2

GENERAL PRODUCT INFORMATION

Color: Bronze

CONFIGURATION

Gangs: 2

PRODUCT MEASUREMENTS

Wt. Ea. (Lbs.): 0.485

PACKAGING

Package Type: Shrink
Std. Pkg.: 4
Product UPC-A Labeled: Yes
Weight (Lbs. Per/C): 48.50
Ship Carton Length (in.): 5.12
Ship Carton Width (in.): 5.31
Ship Carton Height (in.): 6.50
Ctn Weight (Lbs.): 1.94
Pallet Qty: 960.00
UPC Number: 092326112802
I2of5: 30092326112803