

DATE: \_\_\_\_\_ TYPE: \_\_\_\_\_

NAME: \_\_\_\_\_

PROJECT: \_\_\_\_\_

Incandescent

# P3474-09

## Trinity

Three-light hall and foyer fixture featuring soft angles, curving lines and etched glass shades. Gracefully exotic, the Trinity Collection offers classic sophistication for transitional interiors. Sculptural forms of metal and glass are enhanced by a classic finish. This transitional style can transform a room or your whole home with its charming versatility.

**Category:** Hall & Foyer

**Finish:** Brushed Nickel (plated)

**Construction:** Steel construction

**Glass:** Etched glass inverted bowl style



**Diameter:** 18"  
**Height:** 24"  
**Overall ht. w/chain:** 99"

**Glass:** 16" dia.  
**Height:** 5-1/2"

| MOUNTING   | ELECTRICAL                                    | LAMPING   | ADDITIONAL INFORMATION   |
|--|---|---|--|
| Ceiling chain mounted<br>Mounting strap for outlet box included<br>Canopy covers a standard 4" hexagonal recessed outlet box | Pre-wired<br>15 feet of wire supplied<br>120V | Quantity: 3<br>100W Medium Base<br>Medium porcelain sockets | UL-CUL Damp location listed<br>1 year warranty<br>Companion Bath and Vanity, Chandelier, Close-to-ceiling, Hall and Foyer, Pendant, Wall bracket, fixtures are available |

DATE: \_\_\_\_\_ TYPE: \_\_\_\_\_

NAME: \_\_\_\_\_

PROJECT: \_\_\_\_\_

Incandescent

# P3474-09

## Trinity

Three-light hall and foyer fixture featuring soft angles, curving lines and etched glass shades. Gracefully exotic, the Trinity Collection offers classic sophistication for transitional interiors. Sculptural forms of metal and glass are enhanced by a classic finish. This transitional style can transform a room or your whole home with its charming versatility.

**Category:** Hall & Foyer

**Finish:** Brushed Nickel (plated)

**Construction:** Steel construction

**Glass:** Etched glass inverted bowl style



**Diameter:** 18"  
**Height:** 24"  
**Overall ht. w/chain:** 99"

**Glass:** 16" dia.  
**Height:** 5-1/2"

| MOUNTING   | ELECTRICAL  | LAMPING   | ADDITIONAL INFORMATION   |
|--|---|---|--|
| Ceiling chain mounted<br><br>Mounting strap for outlet box included<br><br>Canopy covers a standard 4" hexagonal recessed outlet box | Pre-wired<br><br>15 feet of wire supplied<br><br>120V | Quantity: 3<br>100W Medium Base<br><br>Medium porcelain sockets | UL-CUL Damp location listed<br><br>1 year warranty<br><br>Companion Bath and Vanity, Chandelier, Close-to-ceiling, Hall and Foyer, Pendant, Wall bracket, fixtures are available |