



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## **PDG13M0030TFFJ PDG1 3P 30A 65KA/480V Fxfxtmtu** *Eaton Corp*

|                  |                                                                                                                                                             |
|------------------|-------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Catalog Number   | PDG13M0030TFFJ                                                                                                                                              |
| Manufacturer     | Eaton Corp                                                                                                                                                  |
| Description      | Eaton Power Defense Molded Case Circuit Breaker, Globally Rated, Frame 1, Three Pole, 30A, 65KA/480V, T-M (FXD-FXD) Tu, Standard Line and Load (PDG1X3T125) |
| Weight per unit  | 2.8 (lbs/each)                                                                                                                                              |
| Product Category | 3 Pole                                                                                                                                                      |

### **Features**

|                |                                   |
|----------------|-----------------------------------|
| Current Rating | 30 A                              |
| dimensions     | 2.9921 IN X 3.0000 IN X 5.5000 IN |
| frame          | 1                                 |
| media          | Yes                               |
| Poles          | 3                                 |
| Voltage Rating | 600 VAC                           |

### **Descriptions**

|                        |                                                                                                                                                                                                                                                                                                                                                                                                                                  |
|------------------------|----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Description            | PDG1 3P 30A 65KA/480V FXFXTMTU                                                                                                                                                                                                                                                                                                                                                                                                   |
| extra long description | ETN PDG13M0030TFFJ Power Defense PD                                                                                                                                                                                                                                                                                                                                                                                              |
| Features               | The Power Defense molded case circuit breaker portfolio is globally rated in a small footprint for easy adaptability no matter the application or project requirement. A circuit breaker with communicating electronic trip units and the ability to generate the data to help you optimize your facilities' performance, and to help keep your employees, customers and end-users safe by reducing the risk of arcflash events. |
| Long Description       | Eaton Power Defense molded case circuit breaker, Globally Rated, Frame 1, Three Pole, 30A, 65kA/480V, T-M (Fxd-Fxd) TU, Standard Line and Load (PDG1X3T125)                                                                                                                                                                                                                                                                      |
| Product Type           | Power Defense PDG1 3P 65KA/480V                                                                                                                                                                                                                                                                                                                                                                                                  |

### **Manufacturer Information**

|                           |                |
|---------------------------|----------------|
| Brand                     | Eaton          |
| GTIN                      | 00786679234891 |
| Manufacturers Part Number | PDG13M0030TFFJ |
| UPC                       | 786679234891   |

### **Taxonomies, Classifications, and Categories**

|                      |                              |
|----------------------|------------------------------|
| Category Description | PANELBOARD BOXES & INTERIORS |
| Type                 | Molded case circuit breaker  |



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Packaging

|                 |      |
|-----------------|------|
| Carton          | 1    |
| Weight Per each | 2.75 |

## Uses, Certifications, and Standards

|             |                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                             |
|-------------|---------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Application | Generation - Renewable Energy - Alternative Energy Vehicles:<br>On-Road Generation - Conventional Energy - Conventional<br>Energy Stationary Mach Equip In Factory - Robotics Utility -<br>Substations, Utility Transmission and Distribution Marine Vessels<br>and Equipment - Marine Vessels and Equipment -<br>Other Aviation Vehicles: Vocational - Vehicle: Vocational -<br>Other Mobile Machinery and Equipment - Mobile Machinery and<br>Equipment - Other Elec Assemblies, Panels & OEM - Electrical<br>Assemblies, Panels and OEMs |
| standard    | UL 489, CCC Marked, IEC 60947-2, CSA, RoHS Compliant                                                                                                                                                                                                                                                                                                                                                                                                                                                                                        |