



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



PLG50S 1/2" Square Head Plug

Appleton/Oz Gedney

Catalog Number	PLG50S
Manufacturer	Appleton/Oz Gedney
Description	Unilets Square Head Close-Up Plug, Size: 1/2 In, Material: Steel, Finish: Zinc Electroplate, Connection: Tapered MNPT, Standard: UI 886 (1203), UI File Number E10444, Csa C22.2 No. 25 and 30, Csa 065181, UI Listed For Class I, Groups A, B
Weight per unit	0.1000 (lbs/each)
Product Category	Bar Hangers & Outlet Box Accy.

Features

connection	Tapered MNPT
Material	Steel

Material, Color, and Finish

Finish	Zinc Electroplate
--------	-------------------

Dimensions and Weight

Size	1/2
------	-----

Descriptions

Description	1/2" SQUARE HEAD PLUG
extra long description	APP PLG-50S PLUG 1/2 SQR HEAD CLOS
Long Description	UNILETS Square Head Close-Up Plug, Size: 1/2 IN, Material: Steel, Finish: Zinc Electroplate, Connection: Tapered MNPT, Standard: UL 886 (1203), UL File Number E10444, CSA C22.2 No. 25 And 30, CSA 065181, UL Listed For Class I, Groups A, B
Product Type	Plug 1/2 SQR Head Close-Up
Special Features	Accurately tapped, tapered threads for tight, rigid joints and ground continuity;Explosionproof, dust-ignitionproof;Smooth, rounded integral bushing in each hub protects conductor insulation

Manufacturer Information

Brand	Appleton
GTIN	00781381651905
Manufacturers Part Number	PLG-50S
UPC	781381651905

Taxonomies, Classifications, and Categories

Category Description	Locknuts, Bushings, Re-Bushings, Re-Washers, Threaded Plugs, Knockout Plugs
Type	Square Head Close-Up Plug



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Packaging

Carton	50
Package	500
Weight Per each	0.1

Uses, Certifications, and Standards

Application	For Use With Threaded Rigid Metal Conduit and IMC
standard	And Class III;Class II, Groups E, F, G;UL 886 (1203), UL File Number E10444, CSA C22.2 No. 25 And 30, CSA 065181, UL Listed For Class I, Groups A, B, C, D