



# ROOFTOP PYRAMID ST FIXED STRUT SUPPORT, 10" X 4.8"

## CATALOG NUMBER

**PSF10C**



## CERTIFICATIONS



## FEATURES

Provides superior support for pipe, conduit, cable tray and equipment
Foam bottom offers low abrasion interface for better roof membrane protection
Compatible with roof surfaces including single ply, bituminous, metal and spray foam
Provides superior load distribution, even with varying rooftop surfaces
Ready to use out of the box, saving installation time and labor
Multiple sizes and load ratings offer the ability to tailor the solution to the application
Easy to transport to the roof
Hot-dip galvanized and UV stabilized for long lasting performance

## PRODUCT ATTRIBUTES

Material: Polyethylene; Polypropylene; Steel
Finish: Hot-Dip Galvanized
Temperature: -50 to 150 °F

Static Load Safety Factor: 3:1

Length 1 (L1): 10"

Length 2 (L2): 12 1/2"

Height (H): 4.8"

Width (W): 8"

Surface Area: 92in<sup>2</sup>

Unit Weight: 2 lb

Static Load (F): 1000lb


## ADDITIONAL PRODUCT DETAILS

---

Static load at 73.1 kPa (10.6 psi) roof loading. Contact project or roofing engineer for maximum allowable load on individual project roof system.

## DIAGRAMS

---



## WARNING

---

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at [www.nvent.com](http://www.nvent.com) and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

#### North America

+1.800.753.9221

Option 1 – Customer Care

Option 2 – Technical Support

#### Europe

Netherlands:

+31 800-0200135

France:

+33 800 901 793

#### Europe

Germany:

800 1890272

Other Countries:

+31 13 5835404

#### APAC

Shanghai:

+ 86 21 2412 1618/19

Sydney:

+61 2 9751 8500



Our powerful portfolio of brands:  
**nVent.com CADDY ERICO HOFFMAN RAYCHEM SCHROFF**  
**TRACER**



# ROOFTOP PYRAMID ST FIXED STRUT SUPPORT, 10" X 4.8"

## CATALOG NUMBER

**PSF10C**



## CERTIFICATIONS



## FEATURES

Provides superior support for pipe, conduit, cable tray and equipment
Foam bottom offers low abrasion interface for better roof membrane protection
Compatible with roof surfaces including single ply, bituminous, metal and spray foam
Provides superior load distribution, even with varying rooftop surfaces
Ready to use out of the box, saving installation time and labor
Multiple sizes and load ratings offer the ability to tailor the solution to the application
Easy to transport to the roof
Hot-dip galvanized and UV stabilized for long lasting performance

## PRODUCT ATTRIBUTES

Material: Polyethylene; Polypropylene; Steel
Finish: Hot-Dip Galvanized
Temperature: -50 to 150 °F

Static Load Safety Factor: 3:1

Length 1 (L1): 10"

Length 2 (L2): 12 1/2"

Height (H): 4.8"

Width (W): 8"

Surface Area: 92in<sup>2</sup>

Unit Weight: 2 lb

Static Load (F): 1000lb


## ADDITIONAL PRODUCT DETAILS

---

Static load at 73.1 kPa (10.6 psi) roof loading. Contact project or roofing engineer for maximum allowable load on individual project roof system.

## DIAGRAMS

---



## WARNING

---

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at [www.nvent.com](http://www.nvent.com) and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

#### North America

+1.800.753.9221

Option 1 – Customer Care

Option 2 – Technical Support

#### Europe

Netherlands:

+31 800-0200135

France:

+33 800 901 793

#### Europe

Germany:

800 1890272

Other Countries:

+31 13 5835404

#### APAC

Shanghai:

+ 86 21 2412 1618/19

Sydney:

+61 2 9751 8500



Our powerful portfolio of brands:  
**nVent.com CADDY ERICO HOFFMAN RAYCHEM SCHROFF**  
**TRACER**