



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## PSG120F24RM PSG PWR Supply

Eaton Corp

Catalog Number	PSG120F24RM
Manufacturer	Eaton Corp
Description	Eaton PSG Power Supply, Aluminum, 100-240 Vac, 47-63 HZ, Finger-Safe Terminals, 24 VDC Output, Three-Phase, 960W Output Power, -25°C-75°C Operating Temp
Weight per unit	1.2 (lbs/each)
Product Category	DC Power Supplies

### Features

dimensions	6.0000 IN X 6.5000 IN X 2.5000 IN
media	Yes
Phase	Three-phase

### Descriptions

Description	PSG PWR SUPPLY
extra long description	ETN PSG120F24RM PSG Power Supply
Features	The PSG line of general purpose power supplies is used in a wide variety of industrial control applications. Applications include communication networks, sensors, PLCs and many other electrical systems. Each model is equipped with the options of a rugged metal or plastic housing, heavy-duty screw or finger-safe terminals and a variety of protection features. The PSG line offers the flexibility of operating with a universal input voltage of 100–240 Vac. It also provides system protection and continuous oper
Long Description	Eaton PSG Power Supply, Aluminum, 100-240 Vac, 47-63 Hz, Finger-safe terminals, 24 Vdc output, Three-phase, 960W output power, -25°C-75°C operating temp
Product Type	PSG Power Supply

### Manufacturer Information

Brand	Eaton
GTIN	00786685683584
Manufacturers Part Number	PSG120F24RM
UPC	786685683584

### Taxonomies, Classifications, and Categories

Category Description	POWER SUPPLIES
Type	General purpose power supply

### Availability

Status	Inactive
--------	----------



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Packaging

Carton ..... 1

Weight Per each ..... 1.2

## Uses, Certifications, and Standards

Application ..... Ind Facilities & Factories - Facility: Power Distribution and Control

Frequency Rating ..... 47-63 Hz

standard ..... CSA Std. C22.2,EN Listed,IEC Rated,UL 508,CE Marked,RoHS  
Compliant