



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## PSG960F24RM P.S. 3PH 24VDC 960W IP20 Term Metal *Eaton Corp*

Catalog Number	PSG960F24RM
Manufacturer	Eaton Corp
Description	General Purpose Power Supply, 400-500 Vac, 47-63 HZ, Three-Phase, Din Rail Mount, -20C-75C Operating Temp, Aluminum, 960W, 24 VDC ( $\pm 4.8$ VDC), 24 VDC/2.5A, IP20.
Weight per unit	4.8 (lbs/each)
Product Category	DC Power Supplies

### Features

dimensions	6.5000 IN X 6.2500 IN X 8.0000 IN
Material	Aluminum
media	Yes
Phase	Three-phase
Wattage	960W

### Descriptions

Description	P.S. 3PH 24VDC 960W IP20 TERM METAL
extra long description	ETN PSG960F24RM P.S. 3PH 24VDC 960W
Features	The PSG line of general purpose power supplies is used in a wide variety of industrial control applications. Applications include communication networks, sensors, PLCs and many other electrical systems. Each model is equipped with the options of a rugged metal or plastic housing, heavy-duty screw or finger-safe terminals and a variety of protection features. The PSG line offers the flexibility of operating with a universal input voltage of 100-240 Vac. It also provides system protection and continuous oper
Long Description	General Purpose Power Supply, 400-500 Vac, 47-63 Hz, Three-Phase, DIN rail mount, -20C-75C operating temp, Aluminum, 960W, 24 Vdc ( $\pm 4.8$ Vdc), 24 VDC/2.5A, IP20.
Product Type	P.S. 3PH 24VDC 960W IP20 Term Metal

### Manufacturer Information

Brand	Eaton
GTIN	00786685683614
Manufacturers Part Number	PSG960F24RM
UPC	786685683614

### Taxonomies, Classifications, and Categories

Type	General purpose power supply
------	------------------------------



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Packaging

Carton	1
Weight Per each	4.81

## Uses, Certifications, and Standards

Application	Commercial / Institutional Buildings / Structures - Commercial / Institutional Buildings / Structures - Other
Frequency Rating	47-63 Hz
standard	EN 61000-6-4,EN 61000-406,EN 60204,EN 50178,IEC Rated,EN 61000-4-11,UL 508,EN 61000-4-2,EN 610003-2,PELV (EN 60204),EN 61000-6-2,SELV (EN 60950),CSA Certified,cULus/UL 60950-1,RoHS Compliant,CE Marked,DIN 57100-410,German Safety